






NOTES

1) APPLICABLE PANEL A) HOLE DIAMETER : 7.2^{±0.2}X10.2^{±0.2}(SLOT)
B) THICKNESS : t=0.6~2.0

2) MATING CONNECTOR : 7282-4926 ETC.

注記

1) 適用パネル A) 孔径 : 7.2^{±0.2}X10.2^{±0.2}(長円)

B) 板厚 : t=0.6~2.0

2) 嵌合コネクタ : 7282-4926 ETC.

00.08.10	CORRECTED ERROR	C00-H041	W.O
93.10.18	NEW	C93-H511	W.O
LET DATE	REVISION RECORD	NO.	CHKD

GENERAL TOLERANCE									
10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECENT			
±0.15	±0.2	±0.3	±0.5	±0.75	±30°	0.1			
±0.2	±0.3	±0.5	±0.55	±1.4	±30°	0.1			
±0.3	±0.5	±0.8	±1.4	±2	±30°	0.15			
SPECIFIED							WEIGHT	1.7 g	

CUSTOMER	PART NO.	CUSTOMER	DWG NO.
OFFICE		TRIAL PART NO.	
VENDOR		TRIAL PART NO.	
DWG TYPE	DWG SOURCE	DWG DATE	UNIT
R	NEW	93.10.18	mm
APPROVED	CHECKED	DESIGN	DRAWN
YAZAKI	YAZAKI	YAMAGUCHI	YAZAKI
00.08.21	00.08.21	93.08.17	00.08.10

MATL. P. P. (GRAY)	TREAT.	ISSUE MARK
SPEC.	& FIN.	
NAME	CLIP	
PART NO.	7147-5879-40	
CH. CODE	7147-5879-40:R	
DWG NO.	7147-5879-40:R	
SET DWG NO.		
YAZAKI CORPORATION		