



NO. YAZAKI PARTS NO.		PANEL THICKNESS	DIMENSION A		DIMENSION B		MATERIAL	COLOR		MASS(kg)	TYPE
a	7147-8940	1.0~4.9	6.0	14.5				NATURAL		0.001	9mm
b	7147-8941-40	5.0~8.4	9.5	18.0				GRAY			
c	7147-8942-30	8.5~12.4	13.5	22.0				BLACK			
d	7147-8943	12.5~16.4	17.5	26.0	66NYLON			NATURAL	0.002		17mm
e	7147-8944	1.0~4.9	6.0	14.5				GRAY			
f	7147-8945-40	5.0~8.4	9.5	18.0				BLACK			
g	7147-8946-30	8.5~12.4	13.5	22.0				NATURAL	0.003		
h	7147-8947	12.5~16.4	17.5	26.0				NATURAL			

注 記
1) 本部品は、090-2コネクタ-に装着可能なクリップである。
2) 適用パネル穴径は $\phi 9.5^{+0.5}_{-0.2}$ 、板厚は上表による。

NOTES
1) THESE PARTS ARE CLIPS FOR 090-2 TYPE CONNECTOR.
2) APPLICABLE PANEL HOLE DIAMETER $\phi 9.5^{+0.5}_{-0.2}$ THICKNESS: SEE TABLE

01.02.09	NEW	C01-1018	Y.M
LET	DATE	REVISION RECORD	NO.
1			CHKD

GENERAL TOLERANCE									
A	±0.15	B	±0.2	C	±0.3	10MAX	50MAX	100MAX	250MAX
B	±0.2	C	±0.3	10MAX	50MAX	100MAX	250MAX	500V/R	ANGLE
C	±0.3	10MAX	50MAX	100MAX	250MAX	500V/R	ANGLE	ECCENT	
SPECIFIED	±0.3	±0.5	±0.8	±1.4	±2	±30°	±30°	0.1	
MASS	SEE TABLE #								

CUSTOMER PART NO.		CUSTOMER DWG NO.		MATERIAL SPEC.		TREAT. & FIN.		ISSUE MARK	
OFFICE		TRIAL PART NO.		NAME		CONNECTOR CLIP 090-2			
VENDOR NO.		X30047-0199 ETC.							
DWG. TYPE		DWG. SOURCE		DWG. DATE		UNIT		SCL	
R		NEW		01.02.09		17mm		2:1	
CHECKED		CHECKED		DESIGN		DRAWN		DWG NO.	
K. MATSUHARA		K. MATSUHARA		Y. MATSUHARA		7147-8940:R		SET DWG NO.	
01.02.14		01.02.12		00.12.26		01.02.09		YAZAKI CORPORATION	

1

2

3

4

5

10