


	1	2	3	4	5	6	7
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT
TOLERANCE	±0.5	±0.8	±1.5	±2.5	±3	±5°	0.3



								CUSTOMER						MATL. SWRCH8R~10R				TREAT. TIN PLATING					
								CUSTOMER PART NO.				CUSTOMER DWG NO.				SPEC. (JIS G 3507)				& FIN.			
	00.02.18	NEW				C00-0047	M. S	OFFICE				TRIAL PART NO.				NAME NUT							
LET	DATE	REVISION RECORD				NO.	CHKD	VENDOR								-----							
GENERAL TOLERANCE							VENDOR NO.																
	10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT	DWG TYPE		DWG SOURCE		DWG DATE		UNIT	SCL	ANGLE	PART NO.						
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	R		NEW		00.02.18		mm	2:1	3	7151-1053-02						
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED		CHECKED		CHECKED		DESIGN		DRAWN		DWG NO.					
C	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15	鈴木 泰隆		鈴木 勝也		M. SUZUKI		M. SUZUKI				7151-1053-02:R					
SPECIFIED							MASS		00.02.18		00.02.18		00.02.18		00.02.18		00.02.18		SET DWG NO.				
SEE TABLE							APPROX. 3.5 g												YAZAKI CORPORATION				