





PLASTIC GENERAL TOLERANCE		
	A	(B)
0 TO 1	± 0.10	± 0.20
~ TO 3	± 0.11	± 0.21
~ TO 6	± 0.12	± 0.22
~ TO 10	± 0.14	± 0.24
~ TO 15	± 0.17	± 0.27
~ TO 22	± 0.20	± 0.30
~ TO 30	± 0.24	± 0.34
~ TO 40	± 0.28	± 0.38
~ TO 53	± 0.33	± 0.43
~ TO 70	± 0.40	± 0.50
~ TO 90	± 0.50	± 0.60
~ TO 120	± 0.60	± 0.70
~ TO 160	± 0.75	± 0.85
~ TO 200	± 0.95	± 1.05
~ TO 250	± 1.15	± 1.25
~ TO 315	± 1.45	± 1.55
~ TO 400	± 1.80	± 1.90
~ TO 500	± 2.20	± 2.30
~ TO 630	± 2.80	± 2.90
~ TO 800	± 3.50	± 3.60
~ TO 1000	± 4.40	± 4.50
ANGLE	± 30"	± 1°

NO.	PART NO.	PART NAME	MASS(g)
①	7176-1878-30	INMANI (82126) PROTECTOR BASE	(22.6)
②	7176-0997-30	INMANI (82126) PROTECTOR COVER	(8.9)

NOTE
1) GENERAL THICKNESS : 1.5

注記
1) 一般肉厚:1.5



DELIVERY FORM

16.11.03	NEW	C16-G069	D.A
LET	DATE	REVISION RECORD	NO.
			CHKD

GENERAL TOLERANCE						
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE
A	± 0.15	± 0.20	± 0.30	± 0.50	± 0.75	± 30°
B	± 0.20	± 0.30	± 0.55	± 0.95	± 1.40	± 30°
C	± 0.30	± 0.50	± 0.80	± 1.40	± 2.00	± 30°
SPECIFIED						SEE TABLE g
SEE PLASTIC GENERAL TOLERANCE CLASS = B						MASS

CUSTOMER		CUSTOMER		MATERIAL		TREAT.	
CUSTOMER PART NO.		CUSTOMER DWG NO.		SPEC.		P.(BLACK)	
OFFICE		TRIAL PART NO.		NAME		INMANI (82126)	
VENDER						PROTECTOR BASE	
VENDER NO.							
DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO.	CH. CODE
R	NEW	16.11.03	mm	1/1	3	7176-1878-30 ETC.	
APPROVED	CHECKED	CHECKED	DESIGN	DRAWN		DWG NO.	SET DWG NO.
岡崎	義村	鈴木(通)	SAWAZAKI	DARY		7176-1878-30:R	
						YAZAKI CORPORATION	