



CII

TE Internal #: 4-1617004-0

General Purpose Power Relay, DC, Non-Polarized, Monostable, 2 Form C DPDT-CO, 10 A Contact Rating, 26.5 VDC Coil Voltage, 2.34 W Coil Power

[View on TE.com >](#)

Relays & Contactors > Electromechanical Relays



Relay & Contactor Type: **General Purpose Power Relay**

Coil Magnetic System: **Non-Polarized, Monostable**

Contact Arrangement: **2 Form C DPDT-CO**

Current Type: **DC**

Contact Current Rating: **10 A**

Features

Product Type Features

Relay & Contactor Type	General Purpose Power Relay
------------------------	-----------------------------

Configuration Features

Contact Arrangement	2 Form C DPDT-CO
---------------------	------------------

Electrical Characteristics

Coil Resistance	300 Ω
Contact Switching Voltage (Max)	28 VDC
Contact Current Rating	10 A
Coil Voltage Rating	26.5 VDC
Coil Power Rating DC	2.34 W

Body Features

Enclosure Type	Hermetically Sealed
----------------	---------------------

Contact Features

Contact Material	Silver Cadmium Oxide
------------------	----------------------

Termination Features

Main Termination & Connection Type	Solder Hook Terminals
Coil Termination & Connection Type	Solder Hook Terminals

Mechanical Attachment



Product Mounting Feature Type	Mounting Brackets
-------------------------------	-------------------

Product Mount Type	Chassis Mount
--------------------	---------------

Usage Conditions

Operating Temperature Range	-65 – 125 °C
-----------------------------	--------------

Environmental Ambient Temperature (Max)	125 °C[257 °F]
---	----------------

Operation/Application

Vibration Resistance	20G's, 10 – 2000Hz
----------------------	--------------------

Shock Resistance	100G's, 6ms
------------------	-------------

Coil Magnetic System	Non-Polarized, Monostable
----------------------	---------------------------

Current Type	DC
--------------	----

Other

Contact Current Class	>5 – ≤10 A
-----------------------	------------

Coil Power Rating Class	>1.5 – ≤3 W
-------------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
------------------------------	---------------

EU ELV Directive 2000/53/EC	Not Compliant
-----------------------------	---------------

China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
---	--------------------------------------

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Cd (2.75% in Component Part) <b>Article Safe Usage Statements:</b> Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
--	---

Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	--

Solder Process Capability	Not lead free process capable
---------------------------	-------------------------------

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 1-1617754-7  
[FCA-410-1620M=M83536/16-020M](#)


Customers Also Bought



TE Part #9908044002  
[DR-25-TW-1/2-0-SP](#)



TE Part #800612-SF  
[FN2020-20-06](#)



TE Part #806748-000  
[222D132-25-0](#)



TE Part #1-338168-2  
[9POL HDP20 PLUG](#)



TE Part #3-1617033-0  
[HFW1230K06M = M39016/6-105M](#)



TE Part #1617126-3  
[JMAWD-18XL = M39016/15-032L](#)



TE Part #2-1623930-9  
[CFR25 5% 1K0](#)



TE Part #1757819-5  
[AMPLIMITE,ASY,PLUG,STD,109,ZN,5](#)



TE Part #1757820-5  
[AMPLIMITE,ASY,RCPT,STD,109,ZN,5](#)



TE Part #3-1879337-0  
[CPF 0603 4K99 1% 50PPM 1K RL](#)



Documents

Product Drawings

B07D932BC2-0348 = M5757/23-031

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_4-1617004-0\_C.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_4-1617004-0\_C.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_4-1617004-0\_C.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

5-1773450-5\_sec1\_07

English

RELAY

English