





GENERAL TOLERANCE									
10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE
±0.15	±0.2	±0.3	±0.5	±0.75	±0.2	±0.3	±0.5	±2.5	±3°
±0.2	±0.3	±0.55	±0.95	±1.4	±0.2	±0.3	±0.5	±3°	0.1
±0.3	±0.5	±0.8	±1.4	±2				±3°	0.15

SUB ASSEMBLY PART NO. AND CH. CODE		NO.	PART NO. AND CH. CODE	PART NAME	MATERIAL	COLOR	QTY.
7283-0764-30 7287-0138-30		①	7183-0764-30	HOUSING	PBT-g	BLACK	1
		②	7158-6943	FRONT HOLDER	PBT	NATURAL	1
		③	7137-2043-80	PACKING	SILICONE RUBBER	BROWN	1
		④	7158-9553	LEVER	PBT-g	NATURAL	1





SEC. A-A



△ 7283-0764-30

△ 7287-0138-30



- 注記
1. かん合相手品番 : 7282-0764-30
 2. 適用端子品番 : 7116-5073-02
 3. 適用J A栓品番 : 7158-3610-80, 7158-3611-60

NOTES

1. MATING PART NO. : 7282-0764-30
2. APPLICABLE TERMINAL NO. : 7116-5073-02
3. APPLICABLE RUBBER SEAL NO. : 7158-3610-80, 7158-3611-60

4/	10/11/15	CHANGED PART NAME	C10-ZA92	F. V			
3/	07/03/13	CHANGED FORM, ETC.	C07-Z097	S. M			
2/	06/05/12	CHANGE FORM	C06-Z554	M. S			
1/	06/02/22	CHANGE FORM, ETC.	C06-Z184	T. T			
	05/12/14	NEW	C05-Z621	T. T			
LET	DATE	REVISION RECORD	NO.	CHKD			
GENERAL TOLERANCE							
	10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°	0.1
C	±0.3	±0.5	±0.8	±1.4	±2	±30°	0.15
SPECIFIED						MASS	g

CUSTOMER		CUSTOMER PART NO.		CUSTOMER DWG NO.	
OFFICE		OFFICE		TRIAL PART NO.	
VENDOR		VENDOR		VENDOR NO.	
DWG TYPE		DWG SOURCE		DWG DATE	
R		NEW		05/12/14	
APPROVED		CHECKED		DESIGN	
S. MI ZUSE		R. GABANGAL		S. KOMINE	
10/11/15		10/11/15		05/11/16	

MATL.	SEE TABLE	TREAT.	ISSUE MARK
SPEC.		& FIN.	
NAME			
△ 9.5(375) 3P SEALED LIF HOUSING			
SUB ASSEMBLY FEMALE			
PART NO.			
△ 7283-0764-30 ETC.			
DWG NO.			
7283-0764-30:R			
SET DWG NO.			
YAZAKI CORPORATION			