

3

2




### CAVITY 1

## CAVITY 6


### CAVITY 7

## CAVITY 12

( SEE TABLE ) g

E

(2/1)



REAR ISOMETRIC VIEW  
(2/1)

1. PARTS MUST BE PURCHASED FROM YAZAKI.
2. PARTS MUST BE FREE OF FLASH AND IMPERFECTIONS THAT AFFECT FUNCTION.
3. APPLICABLE TERMINAL: SEE 7116-4720-02:R DRAWING (YESC 0.64 UNSEALED)  
MAX WIRE OD: 2.20mm
4. MATING PART NUMBER: 7282-7696-40
5. PART SATISFIES USCAR-2, REVISION 3, APRIL 2001, (T2/V1/S1) WITH THE FOLLOWING EXCEPTIONS:
  - 5.4.2 HOUSING LOCK FORCE TO SERVICE = 6.10N MIN
  - 5.4.4 TPA PRE-SET TO FULL INSTALL WITHOUT TERMINALS = 7.70N MIN
  - 5.4.4 TPA FULL INSTALL TO PRE-SET AFTER INITIAL REMOVAL = 11.70N
  - 5.4.4 CPA PRE-SET TO FULL INSTALL WITH MATED CONNECTOR = 44.80N MAX
  - 5.4.4 CPA REMOVAL FROM HOUSING = 27N MIN
6. PART TO COMPLY WITH YPES-31-038 REQUIREMENTS.
7. THIS DIMENSION SHOWS THE PRE-SET POSITION OF THE SIDE SPACER.
8. THIS DIMENSION SHOWS THE PRE-SET POSITION OF THE CPA.
9. THIS DRAWING IS TO BE USED FOR INTERNAL YAZAKI PSW SUBMISSION.
10. HANDLING MANUAL NUMBER: YPES-15-563E

IKDA