





SUB ASSEMBLY PART NO. AND CH. CODE		PART NO. AND CH. CODE	PART NAME		MATERIAL	COLOR	QTY.
7288-4103-40, [A]		①	7188-4103-40	0.64 II 38P+1.5 25P HYBRID HOUSING MALE	PBT	GRAY	1
		②	7172-1033	0.64 II 38P+1.5 25P HYBRID SPACER MALE	PBT	NATURAL	1
		③	7172-1034	0.64 II 38P+1.5 25P HYBRID ALIGNING PLATE MALE	PBT	NATURAL	1




注記
1. 取扱説明書No. : YPES-15-1469

NOTE
1. HANDLING MANUAL NO. : YPES-15-1469



SEC. A-A



GENERAL TOLERANCE									
10 MAX	50 MAX	100 MAX	250 MAX	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECCENT
A ±0.15	±0.2	±0.3	±0.5	±0.75	±0.3	±0.5	±2.5	±3°	0.1
B ±0.2	±0.3	±0.55	±0.95	±1.4	±0.2	±0.3	±0.5	±3°	0.1
C ±0.3	±0.5	±0.8	±1.4	±2				±3°	0.15

						CUSTOMER		CUSTOMER PART NO.		CUSTOMER DWG NO.		MATL. SPEC.		SEE TABLE		TREAT. & FIN.	
		2015/01/09		NEW, [A]		C14-Z781		K. T				NAME		0.64 II 38P+1.5 25P HYBRID HOUSING			
ET	DATE	REVISION RECORD		NO.		CHKD				TRIAL PART NO.							
		GENERAL TOLERANCE						VENDOR NO.									
		10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO.	7288-4103-40, [A]	
		A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	O. 1	R	NEW	2015/01/09	mm	1 : 1	3	CH. CODE	
SPECIFIED		B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	O. 1	APPROVED	CHECKED	DESIGN	DRAWN	DWG NO.	7288-4103-40:R		SET DWG NO.
		C	±0.3	±0.5	±0.8	±1.4	±2	±30'	O. 15	S. SUZUKI	M. NAGANO	T. SHIMIZU	K. KAWASHIMA	K. TOBIAS			
		MASS		2015/01/09		2015/01/09		2015/01/09		2014/04/22		2015/01/09		YAZAKI CORPORATION			