

7289-9870-30

NOTES:

1. PARTS MUST BE PURCHASED FROM YAZAKI
2. PARTS MUST BE FREE OF FLASH AND IMPERFECTIONS THAT AFFECT FUNCTION.
3. APPLICABLE TERMINAL: SEE 13849927 DRAWING (1.5mm APTIV OCS UNSEALED)
MAX WIRE OD: 2.80mm (APPLICABLE CAVITIES 1-4)
SEE 7116-4120-02-R DRAWING (6.3mm YESC UNSEALED)
MAX WIRE OD: 4.20mm (APPLICABLE CAVITIES 5-6)
4. MATING PART NUMBER: 7386-7404-30
5. PART SATISFIES GWWS191, JUNE 2012 (T2V1/1S1MF3).
6. PART TO COMPLY WITH YPEC9-31-038 REQUIREMENTS.
7. THIS DIMENSION SHOWS THE PRE-SET POSITION OF THE CPA.
8. THIS DIMENSION SHOWS THE PRE-SET POSITION OF THE TPA.
9. THIS DRAWING IS TO BE USED FOR INTERNAL YAZAKI PSW SUBMISSION.
10. HANDLING MANUAL NUMBER: YPES-15-599E



-	12-14-2018	NEW	C18-AC92	IM
LET	DATE	REVISION RECORD	NO.	CHKD

GENERAL TOLERANCE											
	10MAX	50MAX	100MAX	250MAX	2500VR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECCEN
A	±0.15	±0.20	±0.30	±0.50	±0.75					±3°	0.1
B	±0.20	±0.30	±0.55	±0.95	±1.40	±0.20	±0.30	±0.50	±2.50	±3°	0.1
Ⓒ	±0.30	±0.50	±0.80	±1.40	±2.00					±3°	0.15
SPECIFIED										MASS	(8.45)

CUSTOMER							ISSUE MARK	
CUSTOMER PART NO.			CUSTOMER DWG NO.				MATL. SPEC.	SEE TABLE
OFFICE YNA			TRIAL PART NO.				TREAT. & FIN.	N/A
VENDOR			NAME 6P (4Px1.5mm OCS + 2Px6.3mm YESC)					
VENDOR NO.			UNSEALED FEMALE CONNECTOR SUB-ASSEMBLY					
DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO.	CH. CODE	
R	7289-9870-30:M 	12-14-2018	mm	5/1	3	7289-9870-30		
APPROVED	CHECKED	CHECKED	DESIGN	DRAWN		DWG NO.	7289-9870-30:R	
			RYAN BARTLETT	ISABEL MUNIZ		YAZAKI CORPORATION		
			08-29-2017	01-31-2019				