







7386-2047-30
KEYWAY A





EXPLODED VIEW
 (2/1)



FOOTPRINT REFERENCE
(2/1)



SECTION A-A



SECTION B-B

- NOTES:**
1. PARTS MUST BE PURCHASED FROM YAZAKI.
 2. PARTS MUST BE FREE OF BURRS AND SHARP EDGES THAT MAY BE DETRIMENTAL TO SATISFACTORY ASSEMBLY, SAFE HANDLING OR FUNCTION OF THE PART.
 3. MATING PART NUMBER: 7287-2047-30
 4. PART SATISFIES USCAR-2, REV. 4, MAY 2004, (T2, V1, S1).
 5. PART TO COMPLY WITH YPES-31-038 REQUIREMENTS.
 6. AFTER BEING PRESSED IN, THE TERMINALS MUST BE FREE OF PLASTIC RESIN.
 7. THE TERMINALS MUST NOT BE LOOSE AFTER BEING INSERTED UNDER PRESSURE.
 8. 3x5, HD 4.0 SCREW RECOMMENDED FOR OPTIONAL HOLE FOR SCREW HOLE MOUNTING FEATURE.
 9. THIS DRAWING IS TO BE USED FOR INTERNAL YAZAKI PSW SUBMISSION.
 10. ACCEPTABLE PCB THICKNESS RANGE = 1.30 to 1.80mm

	08-23-2018	ADDED TABLE 2, NEW PACKAGING OPTION AND NEW TOLERANCES. UPDATES NOTES AND DELETED DIMENSIONS	C18-A778	EH
-	10-22-2008	NEW	C08-AA60	MMR
LET	DATE	REVISION RECORD	NO.	CHKD

GENERAL TOLERANCE											
	10MAX	50MAX	100MAX	250MAX	2500VR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECCEN
A	±0.15	±0.2	±0.3	±0.5	±0.75	±0.2	±0.3	±0.5	±2.5	±3°	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4					±3°	0.1
(C)	±0.3	±0.5	±0.8	±1.4	±2					±3°	0.15
SPECIFIED										MASS	(12.0) g

CUSTOMER							MATL. SPEC.			SEE TABLE			TREAT. & FIN.		N/A		ISSUE MARK		
CUSTOMER PART NO.							CUSTOMER DWG NO.							NAME					
OFFICE YNA							TRIAL PART NO.							24P HYBRID 2x2.8 YESC + 22x0.64 TYCO GEN Y					
VENDOR														UNSEALED PCB MALE (H) HEADER ASSEMBLY					
VENDOR NO.																			
T	DWG TYPE		DWG SOURCE		DWG DATE		UNIT		SCL		ANGLE		PART NO.		CH. CODE				
	R		7386-2047-30:M / 2		10-22-2008		mm		2/1		3		7386-2047-30, ETC.						
	APPROVED		CHECKED		CHECKED		DESIGN		DRAWN				DWG NO.		7386-2047-30:R		SET DWG NO.		
							K. LAZAR												
							04-05-2007												
YAZAKI CORPORATION																			