




Wire Protection & Management > Heat Shrink Shapes > Cable Transitions & Breakouts



Molded Part Shape: **Y Shape**
Number of Branches & Legs: **3**
Material Code: **4**
Material Systems Code: **10**
Adhesive Requirement: **Adhesive Purchased Separately**

Features

Product Type Features

Molded Part Shape	Y Shape
-------------------	---------

Configuration Features

Number of Branches & Legs	3
Adhesive Requirement	Adhesive Purchased Separately

Body Features

Primary Product Material	Polyolefin Flexible Modified
Material Code	4
Material Systems Code	10

Dimensions

Inside Diameter Range (Leg 2)	12.4 – 26.9 mm[.49 – 1.06 in]
Inside Diameter Range (Leg 1)	12.4 – 26.9 mm[.49 – 1.06 in]
Inside Diameter Range (Body)	18 – 38.6 mm[.71 – 1.52 in]

Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
Resistance Protection	Occasional Fluid Exposure

Other

Molded Part Shape Code	382A
Size Code	034



Adhesive Code	S1125
---------------	-------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 890060-000
S1017-1.0X50

Customers Also Bought



TE Part #CW2823-000
R85049/128-3



TE Part #820243-000
462A034-25-0



TE Part #2-31887-1
PIDG R 22-16 COMM 22-18 MIL 10



TE Part #34112
SOLIS R 22-16COMM 22-18MIL 10



TE Part #320093
TERMINAL,SOLIS R 16-14 10




TE Part #1-794221-0
MINI UMN2 SOK 22-18AWG AU LF



TE Part #5-1437567-0
MPG106F=(MSPG) SWITCH
PUSHBUTT



TE Part #1825603-1
BP1532004=Boot,Pushbutton



TE Part #2176397-4
3502 1R3 1%



TE Part #5747841-4
15 MSFL PLUG RA 318 (IN,FM,BL)

Documents

Product Drawings

382A034-4-0

English

Datasheets & Catalog Pages

1654025_Sec4_4

English

Raychem Molded Parts Visual Guide

English

Product Specifications

Product Specification

English