

1200V SiC Power Module Dual Diode Pack

Features

- SiC Schottky Diode
 - Zero reverse recovery
 - Zero forward recovery
 - Temperature independent switching behavior
 - Positive temperature coefficient on V_F
- Low stray inductance
- High junction temperature operation
- All parts tested to greater than 1,400V


Benefits

- Outstanding performance at high frequency operation
- Low loss and low EMI noise
- Very rugged and easy mount
- Internally isolated package (AIN)
- Low junction to case thermal resistance
- Easy paralleling due to positive T_C of V_F
- RoHS compliant

Applications


- Switched-mode power supply
- Induction heater
- Welding equipment
- Charging station

Package



Parallel

Part #	Package	Marking
GHXS100B120S-D3	SOT-227	GHXS100B120S-D3



Maximum Ratings, at $T_j=25\text{ }^{\circ}\text{C}$, unless otherwise specified (per leg)

Characteristics	Symbol	Conditions	Values	Unit
Continuous forward current	I_{F^*}	$T_C=25\text{ }^{\circ}\text{C}$, $T_j=175\text{ }^{\circ}\text{C}$	198	A
		$T_C=128\text{ }^{\circ}\text{C}$, $T_j=175\text{ }^{\circ}\text{C}$	100	
		$T_C=150\text{ }^{\circ}\text{C}$, $T_j=175\text{ }^{\circ}\text{C}$	67	
Surge non-repetitive forward current sine halfwave	I_{FSM}	$T_C=25\text{ }^{\circ}\text{C}$, $t_p=8.3\text{ ms}$	760	A
		$T_C=110\text{ }^{\circ}\text{C}$, $t_p=8.3\text{ ms}$	670	
Non-repetitive peak forward current	$I_{F,max}$	$T_C=25\text{ }^{\circ}\text{C}$, $t_p=10\text{ }\mu\text{s}$	2000**	A
² value	$\int^2$	$T_C=25\text{ }^{\circ}\text{C}$, $t_p=8.3\text{ ms}$	2397	A^2s
		$T_C=110\text{ }^{\circ}\text{C}$, $t_p=8.3\text{ ms}$	1863	
Repetitive peak reverse voltage	V_{RRM}	$T_j=25\text{ }^{\circ}\text{C}$	1200	V
Diode ruggedness		Turn-on slew rate, repetitive	200	V/ns
Power dissipation	P_{tot}^*	$T_C=25\text{ }^{\circ}\text{C}$	674	W
Operating junction temperature	T_j		-55...175	$^{\circ}\text{C}$
Storage temperature	$T_{storage}$		-55...150	$^{\circ}\text{C}$

Notes: *Typical R_{thJC} used

** Limited by testing equipment

1200V-SiC Power Module

Electrical Characteristics at T_j=25 °C, unless otherwise specified

Characteristics	Symbol	Conditions	Unit
DC blocking voltage	V _{DC}	I _R =200μA, T _j =25 °C	1200
Breakdown voltage	V _{BR}	I _R =4mA, T _j =25 °C	1400
Diode forward voltage	V _F	I _F =100A, T _j =25 °C	-
		I _F =100A, T _j =100 °C	-
		I _F =100A, T _j =175 °C	-
Reverse current	I _R	V _R =100V, T _j =25 °C	-
		V _R =100V, T _j =100 °C	-
		V _R =100V, T _j =175 °C	-
		V _R =100V, T _j =200 °C	-
Total capacitance (fsw=1MHz)	Q _C	V _R =100V, T _j =25 °C	-
Total capacitance (fsw=100kHz)	C	V _F =0.7V, T _j =25 °C	-
		V _F =0.7V, T _j =100 °C	-
		V _F =0.7V, T _j =175 °C	-

Thermal and Package Characteristics at T_a=25 °C, unless otherwise specified

Characteristics	Symbol	Unit
Thermal resistance, junction-case	R _{thJC}	-
Mounting torque	M _d	1.1
Terminal connection torque	M _{dt}	-
Package weight	W _t	-
Isolation voltage	V _{ISOL}	2500

Typical Performance





Fig. 1 Forward Characteristics (Left) and Reverse Characteristics (Right)




Fig. 3 Reverse Characteristics (parameterized on Tj)




Fig. 4 Power Derating




Fig. 5 Current Derating




Fig. 6 Capacitance

1200V SiC Power Module

GHXS100B120S-D3




Fig. 7 Capacitive Charge




Fig. 8 Typical Capacitance Stored Energy





Fig. 9 Transient Thermal Impedance

1200V SiC Power Module

GHXS100B120S-D3

Package Dimensions SOT-227



Sym	Millimeters		Inches	
	Min	Max	Min	Max
A	31.67	31.90	1.247	1.256
B	7.95	8.18	0.313	0.322
C	4.14	4.24	0.163	0.167
D	4.14	4.24	0.163	0.167
E	4.14	4.24	0.163	0.167
F	14.94	15.09	0.588	0.594
G	30.15	30.25	1.187	1.191
H	38.00	38.10	1.496	1.500
I	4.75	4.83	0.187	0.190
J	11.68	12.19	0.460	0.480
K	9.45	9.60	0.372	0.378
L	0.76	0.84	0.030	0.033
M	12.62	12.88	0.497	0.507
N	25.15	25.30	0.990	0.996
O	24.79	25.04	0.976	0.986
P	3.02	3.15	0.119	0.124
Q	6.71	6.96	0.264	0.274
R	4.17	4.42	0.164	0.174
S	2.08	2.13	0.082	0.084
T	3.28	3.63	0.129	0.143
U	26.75	26.90	1.053	1.059
V	3.86	4.24	0.152	0.167
W	20.55	26.90	0.809	0.814
X	5.45	5.85	0.215	0.230
Y	3.15	3.66	0.124	0.144
Z	0.00	0.13	0.000	0.005

1200V SiC Power Module

GHXS100B120S-D3

Revision History

Date	Revision	Notes
6/15/2020	1.0	Initial release of preliminary datasheet
8/24/2020	2.0	Updated data
