




Wire Protection & Management > Heat Shrink Shapes > Cable Transitions & Breakouts



Molded Part Shape: **Y Shape**

Number of Branches & Legs: **3**

Material Code: **3**

Material Systems Code: **10**

Adhesive Requirement: **Adhesive Precoat**

Features

Product Type Features

Molded Part Shape	Y Shape
-------------------	---------

Configuration Features

Number of Branches & Legs	3
Adhesive Requirement	Adhesive Precoat

Body Features

Primary Product Material	Semi-Rigid Modified Polyolefin
Material Code	3
Material Systems Code	10

Dimensions

Inside Diameter Range (Leg 2)	3.3 – 6.6 mm[.13 – .26 in]
Inside Diameter Range (Leg 1)	3.3 – 6.6 mm[.13 – .26 in]
Inside Diameter Range (Body)	6.1 – 13.2 mm[.24 – .52 in]

Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
Resistance Protection	Occasional Fluid Exposure

Other

Molded Part Shape Code	382A
Size Code	012

Adhesive Code	42
---------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #622002-000  
D-144-02



TE Part #479613-000  
202A121-25/225-0



TE Part #BKA145N00590200000  
923 EXTENSION, SPEEDTEC-READY



TE Part #823279-000  
382A012-4/42-0






TE Part #815701-SF  
RN212-3.6-02-0M4



TE Part #D369-R33-NS1  
369 3 WAY REC, CRIMP, SKT



TE Part #53425-1  
TERMINAL,PIDG PVF2 R 12-10 10



TE Part #4-1614353-9  
RN 0603 39R2 0.1% 10PPM CUT LENGTH

TE Part #CTS-S12-12  
CONT SOC ASSY

TE Part #YCTJ720E01BC017000  
MODULE ASSY

Documents

Product Drawings

382A012-3/42-0

English

Datasheets & Catalog Pages

1654025\_Sec4\_-3

English

Raychem Molded Parts Visual Guide

English

Product Specifications

Product Specification

English