

9-1415541-3 ✓ ACTIVE

SCHRACK | SCHRACK Power PCB Relay RT1

TE Internal #: 9-1415541-3

General Purpose Power Relay, AC, Monostable, 1 Form A SPST-NO, 12 A Contact Rating, 230 VAC Coil Voltage, SCHRACK Power PCB Relay RT1

[View on TE.com >](#)



Relays & Contactors > Electromechanical Relays



Relay & Contactor Type: **General Purpose Power Relay**

Coil Magnetic System: **Monostable**

Contact Arrangement: **1 Form A SPST-NO**

Current Type: **AC**

Contact Current Rating: **12 A**

Features

Product Type Features

Relay & Contactor Type	General Purpose Power Relay
------------------------	-----------------------------

Configuration Features

Contact Number of Poles	1
Coil Special Features	UL Coil Insulation Class F
Contact Arrangement	1 Form A SPST-NO

Electrical Characteristics

Contact Limiting Short-Time Current	12 A
Contact Limiting Making Current	25 A
Contact Limiting Continuous Current	12 A
Contact Limiting Breaking Current	12 A
Insulation Initial Dielectric Between Open Contacts	1000 Vrms
Contact Switching Voltage (Max)	400 VAC
Coil Resistance	32500 Ω
Coil Power Rating AC	.74 VA

Contact Current Rating	12 A
------------------------	------

Coil Voltage Rating	230 VAC
---------------------	---------

Contact Voltage Rating	250 VAC
------------------------	---------

Insulation Initial Dielectric Between Contacts & Coil	5000 Vrms
---	-----------

Body Features

Product Weight	14 g [.494 oz]
----------------	----------------

Enclosure Type	Flux Resistant Automatic Solder Capable
----------------	---

Contact Features

Contact Plating Material	Gold
--------------------------	------

Contact Material	AgNi90/10
------------------	-----------

Termination Features

Main Termination & Connection Type	Solder Pins
------------------------------------	-------------

Coil Termination & Connection Type	Solder Pins
------------------------------------	-------------

Mechanical Attachment

Product Mount Type	Board Mount
--------------------	-------------

Dimensions

Insulation Clearance Between Contact & Coil	10 mm [.394 in]
---	-----------------

Insulation Creepage Between Contact & Coil	10 mm [.394 in]
--	-----------------

Product Width	12.7 mm [.5 in]
---------------	-----------------

Product Length	29 mm [1.141 in]
----------------	------------------

Product Height	15.7 mm [.618 in]
----------------	-------------------

Usage Conditions

Operating Temperature Range	-40 – 70 °C [-40 – 158 °F]
-----------------------------	----------------------------

Environmental Category of Protection	RTII
--------------------------------------	------

Environmental Ambient Temperature (Max)	70 °C [158 °F]
---	----------------

Operation/Application

Solder Process	Wave Solder Capable
----------------	---------------------

Coil Magnetic System	Monostable
----------------------	------------

Current Type	AC
--------------	----

Packaging Features

Packaging Method	Box & Tube, Carton
------------------	--------------------

Other

	≤1.1 VA
Contact Current Class	>10 – ≤16 A
Height Class (Mechanical)	>14 – ≤16 mm[>.551 – ≤.63 in]
Length Class (Mechanical)	>22 – ≤33 mm[>.866 – ≤1.299 in]
Width Class (Mechanical)	>11 – ≤14 mm[>.433 – ≤.551 in]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2022103-1
 RT17017



TE Part # 1-1415539-2
 PTMR0730



TE Part # 4-1415037-1
 PTMV0730



TE Part # 8-1415035-1
 RT78724




TE Part # 2-1415037-1
 PTMU0730



TE Part # 1415037-2
 PTMD0730 (EM31)



TE Part # 4-1415036-1
 PTMG0730



TE Part # 1415540-8
 RT28816



TE Part # 1860990-1
 RT78601, RELAY SOCKET PCB 3.5MM



TE Part # 7-1415036-1
 PTML0730

Also in the Series | SCHRACK Power PCB Relay RT1



AC Relays(31)



DC Relays(159)



Electromechanical Relays(190)

Customers Also Bought



TE Part #DRC16-70SBE-P013UK
 PLG, 70P, BLK, E, SEAL BOND, B



TE Part #SRK-PC-080-25-601
 PIN, SOLID, SIZE M8, 25mm², AG



TE Part #CAT-H396-CH8172
 DEUTSCH HDP20 Housings



TE Part #K1002956
 Toggle Switch 08-4-1-13



TE Part #K1008699
Relay 26-60-05



TE Part #DTT-20-03
CRIMP TOOL



TE Part #K1007153
Toggle Switch 08-1-1-13



TE Part #K1060489
Relay 29-113-12



TE Part #2-2176245-2
CRGS1206 5% 56R

Documents

CAD Files

Customer View Model

[ENG_CVM_CVM_9-1415541-3_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9-1415541-3_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9-1415541-3_B.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Power PCB Relay RT1

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

VDE Certificate

English