




Connectors > Contacts > Connector Contacts



Contact Type: **Socket**

Contact Mating Area Plating Material: **Tin (Sn)**

Wire Contact Termination Area Plating Material: **Pre-Tin**

Operating Voltage: **250 VAC**

Contact Retention Within Housing: **With**

Features

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Contact Diameter	3.56 mm[.14 in]
Contact Type	Socket
Contact Mating Area Plating Material	Tin (Sn)
Wire Contact Termination Area Plating Material	Pre-Tin
Contact Retention Within Housing	With
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	28 A

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable



Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance
---------------------------------------	---------------

Dimensions

Wire Size	.5 – 1.5 mm ²
Compatible Insulation Diameter Range	1.2 – 2.39 mm[.047 – .094 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Quantity	2500
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2151475-2 OCEAN_2.0_Applicator-S-100F110F-RSA	TE Part # 1-480510-0 04P .140 MNL PLUG NAT	TE Part # 539764-1 EXTRACTION TOOL	TE Part # 7-2151475-7 OCEAN_2.0_SPARE_PART_KIT-100F110F
TE Part # 1-480585-0 09P .140 MNL PLUG NAT	TE Part # 1-480672-0 09P .140 MNL PLUG PM NAT	TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	TE Part # 925451-1 M-N-L SOCKET HSG
TE Part # 1-480672-9 09P .140 MNL PLUG PM BLK	TE Part # 1-350346-0 03P .140 MNL PLUG P/M NAT	TE Part # 1-350344-0 02P .140 MNL PLUG NAT	TE Part # 2151475-1 OCEAN_2.0_Applicator-S-100F110F-RSM
TE Part # 1752938-2 SDE DIE SET 3.5 MM MNL			

Also in the Series | Commercial MATE-N-LOK



Connector Contacts(150)



Crimp Wire Pins, Tabs & Ferrules(2)



Power Contacts(146)



Rectangular Connector Housings(118)



Rectangular Power Connectors(181)




Standard Circular Connectors(2)



Standard Rectangular Connectors(126)


Customers Also Bought




TE Part #172127-1
FF 250 PLUG HSG 1P NYLON NAT



TE Part #172128-1
FF 250 REC HSG 1P NYLON NAT



TE Part #1-350346-0
03P .140 MNL PLUG P/M NAT




TE Part #1-480672-0
09P .140 MNL PLUG PM NAT



TE Part #626094-2
FF .250 REC 0.5 /1.0 MM2 0.32X19.3
TPBR



TE Part #626437-4
ELCETRO TAP ASSY




TE Part #880646-5
PL REC 0.5-1.0 MM2 0.40 X 52.32
PTPBR



TE Part #880687-2
.140 DIA SOCKET



TE Part #925712-1
.140 DIA SOCKET



TE Part #925713-1
M-N-L PIN TPBR

Documents



Product Drawings

MNL BUCHSE 3,5 MM

English

CAD Files

Customer View Model

ENG_CVM_926986-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_926986-2_A.3d_stp.zip

English

Customer View Model

ENG_CVM_926986-2_A.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English