




Heat Shrink Tubing > SST-FR Heat Shrink Tubing



Tubing Product Type: **Heat Shrink Tubing**

Primary Product Color: **Black**

Wall Type: **Single Wall**

Expanded Inside Diameter (Min): **10.16 mm [.4 in]**

Recovered Inside Diameter (Max): **3.81 mm [.15 in]**

[All SST-FR Heat Shrink Tubing \(46\)](#)

Features

Product Type Features

Tubing Product Type	Heat Shrink Tubing
Wall Type	Single Wall

Body Features

Fluid Type	De-Icing Fluid, Hydraulic Fluid, Lubricating Oil, Turbine Fuel
Primary Product Color	Black
Shrink Ratio	3:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Semi-Rigid

Dimensions

Expanded Inside Diameter (Min)	10.16 mm[.4 in]
Recovered Inside Diameter (Max)	3.81 mm[.15 in]
Tubing Size Range	3.81 – 10.16 mm[.15 – .4 in]

Usage Conditions

Resistance Properties	Moisture
Shrink Temperature (Min)	90 °C
Tubing Flammability Type	Flame-Retardant



Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]
Recovery Temperature	121 °C

Operation/Application

Mechanical Resistance	Abrasion, Fluids, Moisture
-----------------------	----------------------------

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Piece
------------------	-------

Other

Meets Low Outgassing Requirements	No
Product Source	Czech Republic

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 955018-000
CLTEQ-M105-TUNNEL-OVEN




TE Part # 2394980-1
MOD 105 TUN OVEN, 69" ENTRY, STARDARD



TE Part # 2326489-1
MODEL 105 TUNNEL OVEN, 36" ENTRY, STANDA

Also in the Series | RAYCHEM SST-SR



Heat Shrink Tubing(44)



Single Wall Tubing(44)

Customers Also Bought



TE Part #1SNA105032R1500
M4/6



TE Part #1SNA115116R0700
M4/6



TE Part #5677612011
RNF-3000-39/13-0-STK



TE Part #1SNA105001R2700
M4/6



TE Part #1SNA105116R1600
M4/6



TE Part #1534805-1
HD20 COVER KIT 9POS WITH CABLE



TE Part #1534807-1
HD20 COVER KIT 15P



TE Part #135933-5
CGPT 2/1 19../ 9.5 1m BLEU



TE Part #1-1103402-1
HA.4.Sti.S



Documents

Product Drawings

[SST-6-04/FR/97](#)

English

Datasheets & Catalog Pages

[SST and SST-FR Pages from 9-1773447-9](#)

English

[Selecting_Correct_Tubing_1216](#)

English

[Application Tooling for Raychem Heat Shrink Product](#)

English

[Measuring_Single_Wall_Tubing](#)

English

Product Specifications

[Quality Specification](#)

English