



Switches > Toggle Switches > Toggle Switch 1-Pole, Sealed, Lever, Toggle, Plastic Lever



Configuration (Pole-Throw): **Single Pole - Double Throw**

Operating Function: **(On) Off (On)**

Number of Positions: **3**

Contact Current Rating: **15 A**

Operating Voltage: **28 VDC**

[All Toggle Switch 1-Pole, Sealed, Lever, Toggle, Plastic Lever \(38\)](#)

Features

Product Type Features

Sealed Device	Yes
Toggle Style	Lever
Switch Type	Toggle Switch

Configuration Features

Configuration (Pole-Throw)	Single Pole - Double Throw
Operating Function	(On) Off (On)
Number of Positions	3

Electrical Characteristics

Contact Current Rating	15 A
Operating Voltage	115 VAC

Body Features

Sealing Method	Strippable Transparent Protective Seal
----------------	--



Product Orientation	Horizontal
Bushing Style	Threaded
Bushing Thread Size	M12 x .75

Contact Features

Contact Base Material	Copper
Switch Contact Plating Material	Silver Tin Oxide

Mechanical Attachment

Product Mount Type	Panel Mount
--------------------	-------------

Housing Features

Process Sealed	Yes
----------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (3.5% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the



product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

 TE Part # CAT-AL8-KSTS081 Toggle Switch 1-Pole, Sealed, Lever, Toggle, Plastic Lever	 TE Part # CAT-AL8-KSTS091 Toggle Switch 1-Pole, Sealed, Lever, Toggle, Metal Lever	 TE Part # K1131165 Toggle Switch 09-4-1-17 926	 TE Part # K1131164 Toggle Switch 09-2-1-17 926
 TE Part # K1021326 Toggle Switch 09-2-1-13 D	 TE Part # K2001914 Toggle Switch 08-4-1-14 F	 TE Part # K1009382 Switch guard 08-0-0-01 902	 TE Part # K1125121 Switch guard 08-0-0-01 915
 TE Part # CAT-AL8-KSTS071 Toggle Switch 1-Pole, Sealed, Lever, Toggle	 TE Part # K1139243 Bellow compl. FMQ 08-80-666	 TE Part # CAT-AL8-KSTS072 Toggle Switch 2-Pole, Sealed, Lever, Toggle	 TE Part # K1158447 Toggle Switch 07-1-2-13 931 Set Conti.
 TE Part # K1000161 Toggle Switch 08-4-1-20 A 940	 TE Part # K1165373 Switch guard 08-0-0-08	 TE Part # K1002958 Toggle Switch 08-4-1-26 A	 TE Part # K1150879 Switch guard 08-0-0-01 with NATO-No





TE Part # K1040743
Toggle Switch 08-4-1-23 A



TE Part # K1145129
Switch guard 07-0-0-01 905



TE Part # K1041435
Switch guard 08-0-0-04 905



TE Part # K1150112
Toggle Switch 07-3-3-99 916


Also in the Series | KISSLING Series 08



Other Automotive Connector Accessories(1)



Switch Seals & Accessories(18)



Toggle Switches(125)

Customers Also Bought



TE Part #CAT-AL8-KSTS082
Toggle Switch 2-Pole, Sealed, Lever, Toggle, Plastic Lever



TE Part #K1002956
Toggle Switch 08-4-1-13



TE Part #CAT-AL8-KSTS081
Toggle Switch 1-Pole, Sealed, Lever, Toggle, Plastic Lever



TE Part #K1140735
Limit switch G12-212-D



TE Part #5-104362-3
04 MTE HDR SRST LATCH W/HLDWN



TE Part #1622820-4
3520 10R 5%



TE Part #5747840-4
HD-20 PLUG RA .318 FMS BD-LK 4

Documents

- Product Drawings
- Toggle Switch 08-1-1-17 E
- English
- Toggle Switch 08-1-1-17 E
- German
- Toggle Switch 08-1-1-17 E



German

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_K1002918_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_K1002918_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_K1002918_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

KISSLING TOGGLE SWITCH Series 08

English