

447-328

Composite Standard Profile EMI/RFI Band-in-a-Can Backshell with Strain-Relief Clamp and Self-Locking Rotatable Coupling




CONNECTOR DESIGNATOR:

A	MIL-DTL-5015, -26482 Series II, and -83723 Series I and III
F	MIL-DTL-38999 Series I, II
L	MIL-DTL-38999 Series 1.5 (JN1003)
H	MIL-DTL-38999 Series III and IV
G	MIL-DTL-28840
U	DG123 and DG123A

SELF-LOCKING

ROTATABLE COUPLING

STANDARD PROFILE



NOTES

1. Metric dimensions (mm) are in parenthesis and are for reference only.
2. Coupling nut supplied unplated.
3. See Table I in Intro for front-end dimensional details.

447-328

Composite Standard Profile EMI/RFI Band-in-a-Can Backshell with Strain-Relief Clamp and Self-Locking Rotatable Coupling


Composite
Backshells

TABLE II: CONNECTOR SHELL SIZE

Shell Size For Connector Designator*					E		F		G		J		K		Max Entry
A	F/L	H	G	U	± .06	(1.5)	± .09	(2.3)	Max	± .06	(1.5)	± .09	(2.3)	Dash No. **	
08	08	09	—	—	.69	(17.5)	.88	(22.4)	1.31	(33.3)	.72	(18.3)	1.15	(29.2)	10
10	10	11	—	08	.75	(19.1)	1.00	(25.4)	1.42	(36.1)	.75	(19.1)	1.27	(32.3)	12
12	12	13	11	10	.81	(20.6)	1.13	(28.7)	1.57	(39.9)	.75	(19.1)	1.33	(33.8)	14
14	14	15	13	12	.88	(22.4)	1.31	(33.3)	1.57	(39.9)	.76	(19.3)	1.37	(34.8)	16
16	16	17	15	14	.94	(23.9)	1.38	(35.1)	1.64	(41.7)	.78	(19.8)	1.39	(35.3)	20
18	18	19	17	16	.97	(24.6)	1.44	(36.6)	1.73	(43.9)	.79	(20.1)	1.41	(35.8)	20
20	20	21	19	18	1.06	(26.9)	1.63	(41.4)	1.82	(46.2)	.82	(20.8)	1.43	(36.3)	22
22	22	23	—	20	1.13	(28.7)	1.75	(44.5)	1.82	(46.2)	.86	(21.8)	1.47	(37.3)	24
24	24	25	23	22	1.19	(30.2)	1.88	(47.8)	1.92	(48.8)	.89	(22.6)	1.50	(38.1)	32
28	—	—	25	24	1.34	(34.0)	2.13	(54.1)	2.00	(50.8)	.92	(23.4)	1.53	(38.9)	32

**Consult factory for additional entry sizes available.

TABLE III: FINISH

Symbol	Finish Description
XM	2000 Hour Corrosion Resistant Electroless Nickel
XMT	2000 Hour Corrosion Resistant Ni-PTFE, Nickel-Fluorocarbon Polymer. 1000 Hour Grey™
XW	2000 Hour Corrosion Resistant Cadmium/Olive Drab over Electroless Nickel

TABLE IV: CABLE ENTRY

Entry Code	H		Entry Dia.*		Clamp Closed	
	±.06	(1.5)	±.03	(0.8)	±.03	(0.8)
10	.94	(23.9)	.22	(5.6)	.26	(6.6)
12	1.17	(29.7)	.28	(7.1)	.34	(8.6)
14	1.28	(32.5)	.34	(8.6)	.46	(11.7)
16	1.41	(35.8)	.46	(11.7)	.55	(14.0)
18	1.50	(38.1)	.55	(14.0)	.62	(15.7)
20	1.56	(39.6)	.62	(15.7)	.70	(17.8)
22	1.69	(42.9)	.70	(17.8)	.78	(19.8)
24	1.81	(46.0)	.78	(19.8)	.85	(21.6)
28	1.91	(48.5)	.85	(21.6)	.95	(24.1)
32	2.02	(51.3)	.95	(24.1)	1.02	(25.9)

* Entry diameter equals maximum wire bundle diameter.