




FOR USE WITH STEEL AND STAINLESS STEEL

PART NUMBER	THREAD SIZE A	B	C	D	E	HOLE SIZE	PLATE THICKNESS	TORQUE VALUE	SETTING TOOL+THREADED INSERT	LONG STEPPED DRILL	SHORT STEPPED DRILL
81963-01	M6	11.5	4.5	6.4	Ø16	11.5/11.7	1.5-4mm	4Nm	PMTc6 + VAV06CV045	OFE1150044	OFE1150018
81965-01	M8	15	5.5	8.7	Ø19.5	15.0/15.2	1-5-4mm	10Nm	PMT8 + VAV08CV050	OFE1500042	OFE1150018
81967-01	M10	19	5.5	9.2	Ø25	19.0/19.2	2-4mm	20Nm	PMT10 + VAV10CV050	OFE1900051	OFE1900022

FOR USE WITH ALUMINIUM

PART NUMBER	THREAD SIZE A	B	C	D	E	HOLE SIZE	PLATE THICKNESS	TORQUE VALUE	SETTING TOOL+THREADED INSERT	LONG STEPPED DRILL	SHORT STEPPED DRILL
81964-01	M6	11.5	4.5	6.4	Ø16	11.5/11.7	1.5-4mm	4Nm	PMTc6 + VAV06CV045	OFE1150044	OFE1150018
81966-01	M8	15	5.5	8.7	Ø19.5	15.0/15.2	1-5-4mm	10Nm	PMT8 + VAV08CV050	OFE1500042	OFE1500018
81968-01	M10	19	5.5	9.2	Ø25	19.0/19.2	2-4mm	20Nm	PMT10 + VAV10CV050	OFE1900051	OFE1900022

MATERIAL	
FINISH	

TITLE

EARTH BOSSES FOR USE WITH
STEEL/STAINLESS STEEL
AND ALUMINIUM (METRIC)

UNLESS STATED OTHERWISE

THE POSITION OF ANY [BASIC] SIZE HOLES
ARE SUBJECT TO THE FOLLOWING
GEOMETRIC TOLERANCES
[Ø] ± 0.20
[] ± 0.08

TOLERANCES
XX ± 0.13
X ± 0.25
HOLES ± 0.08
ANGLES ± 0.5°

DIMENSIONS

mm.

DRAWN BY

A.Jackson

DATE

07/09/06

PROJECTION

A3

DIS

5089

SHT

1

REV

4

REV	B	8768	31/01/08
REV	DOC No.		DATE




GLENAIR UK LTD
OAKHAM BUSINESS PARK
MANNINGFORD ROAD
MANNINGFORD
WILTSHIRE
BA11 1AA
UNITED KINGDOM

THIS DOCUMENT CONTAINS INFORMATION OF A CONFIDENTIAL NATURE AND IS THE PROPERTY OF GLENAIR UK LTD. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED HEREIN. IT IS NOT TO BE REPRODUCED, COPIED, OR IN ANY MANNER DISCLOSED AT ITS OWN PRIVATE EXPENSE AND MAY NOT BE USED, REPRODUCED OR DISCLOSED IN WHOLE OR IN PART FOR DESIGN, MANUFACTURE OR PROCUREMENT OF ANY PRODUCT OR SERVICE WITHOUT THE WRITTEN AUTHORIZATION OF GLENAIR UK LTD. BY RETURNING THE ORIGINAL OF THIS DOCUMENT TO THE ISSUING OFFICE, THE USER AGREES THAT IT SHALL NOT BE USED IN ANY MANNER NOTED HEREIN.

MRP1572

B



FOR USE WITH STEEL AND STAINLESS STEEL PLATE

PART NUMBER	THREAD SIZE	A	B	C	D	E	HOLE SIZE	PLATE THICKNESS	TORQUE VALUE	SETTING TOOL	LONG STEPPED DRILL	SHORT STEPPED DRILL
80923-01	M6	16Ø	21(26)	4.5	4.5	11.5Ø	11.5/11.7	1.5-4mm	8Nm	PM16/PMTC6	OF E1150044	OF E1150018
80974-01	M6	16Ø	13(18)	4.5	4.5	11.5Ø	11.5/11.7	1.5-4mm	8Nm	PMTC6	OF E1150044	OF E1150018
80925-01	M6	16Ø	24(27)	3.5	11	8.5Ø	8.5/8.7	>4mm	8Nm	PM16/PMTC6	OF E0850032	OF E0850016
80975-01	M6	16Ø	16(19)	3.5	11	8.5Ø	8.5/8.7	>4mm	8Nm	PMTC6	OF E0850032	OF E0850016
81929-01	M8	20Ø	15(20)	4.5	4.5	15.0Ø	15.0/15.2	1.5-4mm	15Nm	PM18	OF E1500042	OF E1500018
81928-01	M8	20Ø	19(21)	3.5	11	11.5Ø	11.5/11.7	>4mm	15Nm	PM18	OF E1150044	OF E1150018
80924-01	M10	25Ø	24(31)	5.5	4.5	19.0Ø	19.0/19.2	2.4mm	34Nm	PM110	OF E1900051	OF E1900022
80926-01	M10	25Ø	28(31)	3.5	11	13.5Ø	13.5/13.7	>4mm	34Nm	PM110	OF E1350037	OF E1350019

FOR USE WITH ALUMINIUM PLATE

PART NUMBER	THREAD SIZE	A	B	C	D	E	HOLE SIZE	PLATE THICKNESS	TORQUE VALUE	SETTING TOOL	LONG STEPPED DRILL	SHORT STEPPED DRILL
80958-01	M6	16Ø	21(26)	4.5	4.5	11.5Ø	11.5/11.7	1.5-4mm	8Nm	PM16/PMTC6	OF E1150044	OF E1150018
80976-01	M6	16Ø	13(18)	4.5	4.5	11.5Ø	11.5/11.7	1.5-4mm	8Nm	PMTC6	OF E1150044	OF E1150018
80960-01	M6	16Ø	24(27)	3.5	11	10.5Ø	10.5/10.7	>4mm	8Nm	PM16/PMTC6	OF E1050041	OF E1050020
80977-01	M6	16Ø	16(19)	3.5	11	10.5Ø	10.5/10.7	>4mm	8Nm	PMTC6	OF E1050041	OF E1050020
81931-01	M8	20Ø	15(20)	5.5	4.5	15.0Ø	15.0/15.2	1.5-4mm	15Nm	PM18	OF E1500042	OF E1500018
81930-01	M8	20Ø	19(21)	3.5	11	13.5Ø	13.5/13.7	>4mm	15Nm	PM18	OF E1350037	OF E1350019
80959-01	M10	25Ø	24(31)	5.5	4.5	19.0Ø	19.0/19.2	2.4mm	34Nm	PM110	OF E1900051	OF E1900022
80961-01	M10	25Ø	28(31)	3.5	11	15.0Ø	15.0/15.2	>4mm	34Nm	PM110	OF E1500042	OF E1500018

MATERIAL	
FINISH	

TITLE

EARTH BOND STUDS FOR USE
WITH STEEL/STAINLESS STEEL
AND ALUMINIUM (METRIC)

UNLESS STATED OTHERWISE
THE POSITION OF ANY [BSC] SIZE HOLES
ARE SUBJECT TO THE FOLLOWING
GEOMETRIC TOLERANCES

☒ 0.20
☐ 0.08
ALL DIMENSIONS RELATIVE TO DATUM
GEOMETRIC TOLERANCES

TOLERANCES
XX ± 0.13
X ± 0.25
HOLES ± 0.08
ANGLES ± 0.5°

DIMENSIONS
mm.

DRAWN BY
A.Jackson

DATE
07/09/06

PROJECTION
A3

DIS
5089

SHT
2

REV
4

DATE
31/01/08


REV
B



GLENNAIR UK LTD
OAKHAM BUSINESS PARK
MANSFIELD, NOTTINGHAMSHIRE
UNITED KINGDOM

THIS DOCUMENT CONTAINS INFORMATION
DEVELOPED AT ITS OWN PRIVATE EXPENSE
AND MAY NOT BE USED, DUPLICATED OR
DISCLOSED IN WHOLE OR IN PART FOR
DESIGN, MANUFACTURE OR PROCUREMENT
WITHOUT THE WRITTEN PERMISSION OF
GLENNAIR UK LTD. BY REFERENCE, THE
HOLDER AGREES THAT IT SHALL NOT BE
USED IN ANY MANNER NOTED HEREIN.

MRP1572



FOR USE WITH STEEL AND STAINLESS STEEL

PART NUMBER	THREAD SIZE A	B	C	D	E	HOLE SIZE	PLATE THICKNESS	TORQUE VALUE	SETTING TOOL	STEPPED DRILL
81985-01	1/4"UNC	7/16"	0.177"	0.252"	Ø0.630"	0.437"Ø.445"	0.059"-0.157"	70in-lbf	PMT/C1/4UNC	OFE07/16043
81991-01	3/8"UNC	3/4"	0.216"	0.362"	Ø0.984"	0.750"Ø.758"	0.078"-0.157"	300in-lbf	PMT/3/8UNC	OFE03/04051

FOR USE WITH ALUMINIUM

PART NUMBER	THREAD SIZE A	B	C	D	E	HOLE SIZE	PLATE THICKNESS	TORQUE VALUE	SETTING TOOL	STEPPED DRILL
81986-01	1/4"UNC	7/16"	0.177"	0.252"	Ø0.630"	0.437"Ø.445"	0.059"-0.157"	70in-lbf	PMT/C1/4UNC	OFE07/16043
81992-01	3/8"UNC	3/4"	0.216"	0.362"	Ø0.984"	0.750"Ø.758"	0.078"-0.157"	300in-lbf	PMT/3/8UNC	OFE03/04051

MATERIAL	
FINISH	



GLENNAR UK LTD
OAKHAM BUSINESS PARK
MASTERSFIELD ROAD
OAKHAM
LEICESTERSHIRE
LE12 6JN
UNITED KINGDOM

THIS DOCUMENT CONTAINS INFORMATION OF A CONFIDENTIAL NATURE AND IS THE PROPERTY OF GLENNAR UK LTD. IT IS TO BE KEPT SECRET AND NOT BE USED, REPRODUCED OR DISCLOSED IN WHOLE OR IN PART FOR DESIGN, MANUFACTURE OR PROCUREMENT OF ANY PRODUCT OR SERVICE WITHOUT THE WRITTEN AGREEMENT OF GLENNAR UK LTD. BY RETURNING THIS DOCUMENT TO GLENNAR UK LTD, THE HOLDER AGREES THAT IT SHALL NOT BE USED IN ANY MANNER NOTIFIED HEREIN.

TITLE
EARTH BOSSES FOR USE WITH
STEEL/STAINLESS STEEL
AND ALUMINIUM (IMPERIAL)

UNLESS STATED OTHERWISE
THE POSITION OF ANY [BSC] SIZE HOLES
ARE SUBJECT TO THE FOLLOWING
GEOMETRIC TOLERANCES
ALL DIMENSIONS RELATIVE TO DATUM
ARE SUBJECT TO THE FOLLOWING
GEOMETRIC TOLERANCES

☒ 0.20
☐ 0.08

TOLERANCES
XX = ± 0.13
X = ± 0.25
HOLES = ± 0.08
ANGLES = ± 0.5°


DIMENSIONS
mm.
SCALE 4 : 1

DRAWN BY M.A.P.
DESIGN APPR' M.A.P.

DATE 31/01/08
DATE 31/01/08

PROJECTION
DRAWING No. MRP1572

DIS 5089
REV B
DATE 31/01/08
SHT 3
OF 4
REV B



NOTE
DIMENSION SHOWN IN PARENTHESIS
IS APPROXIMATE LENGTH OF STUD
MEASURED FROM FLANGE FACE.

FOR USE WITH STEEL AND STAINLESS STEEL PLATE

PART NUMBER	THREAD SIZE	A	B	C	D	E	HOLE SIZE	PLATE THICKNESS	TORQUE VALUE	SETTING TOOL	STEPPED DRILL
81983-01	1/4"UNC	Ø0.630"	0.510"(0.700")	0.177"	0.177"	7/16"	0.437"Ø.445"	0.059"-0.157"	70in-lbf	PMT/C1/4UNC	OFE07/16043
81987-01	1/4"UNC	Ø0.630"	0.630"(0.748")	0.138"	0.433"	3/8"	0.375"Ø.383"	>0.157"	70in-lbf	PMT/C1/4UNC	OFE03/08037
81989-01	3/8"UNC	Ø0.984"	0.944"(1.220")	0.216"	0.177"	3/4"	0.750"Ø.758"	0.078"-0.157"	300in-lbf	PMT/3/8UNC	OFE03/04051
81993-01	3/8"UNC	Ø0.984"	1.102"(1.220")	0.138"	0.433"	17/32"	0.531"Ø.539"	>0.157"	300in-lbf	PMT/3/8UNC	OFE17/32037

FOR USE WITH ALUMINIUM PLATE

PART NUMBER	THREAD SIZE	A	B	C	D	E	HOLE SIZE	PLATE THICKNESS	TORQUE VALUE	SETTING TOOL	STEPPED DRILL
81984-01	1/4"UNC	Ø0.630"	0.510"(0.700")	0.177"	0.177"	7/16"	0.437"Ø.445"	0.059"-0.157"	70in-lbf	PMT/C1/4UNC	OFE07/16043
81988-01	1/4"UNC	Ø0.630"	0.630"(0.748")	0.138"	0.433"	7/16"	0.437"Ø.445"	>0.157"	70in-lbf	PMT/C1/4UNC	OFE07/16043
81990-01	3/8"UNC	Ø0.984"	0.944"(1.220")	0.216"	0.177"	3/4"	0.750"Ø.758"	0.078"-0.157"	300in-lbf	PMT/3/8UNC	OFE03/04051
81994-01	3/8"UNC	Ø0.984"	1.102"(1.220")	0.138"	0.433"	19/32"	0.594"Ø.602"	>0.157"	300in-lbf	PMT/3/8UNC	OFE19/32042

C

MATERIAL	
FINISH	

TITLE	
DESCRIPTION	



THIS DOCUMENT CONTAINS INFORMATION OF A CONFIDENTIAL NATURE AND IS NOT TO BE USED, REPRODUCED OR DISCLOSED IN WHOLE OR IN PART FOR DESIGN, MANUFACTURE OR PROCUREMENT OF ANY PRODUCT OR SERVICE WITHOUT THE WRITTEN AUTHORIZATION OF GLENNAR UK LTD. BY REFERENCE, THE HOLDER AGREES THAT IT SHALL NOT BE USED IN ANY MANNER NOTATED HEREIN.

EARTH BOND STUDS FOR USE WITH STEEL/STAINLESS STEEL AND ALUMINIUM (IMPERIAL)

UNLESS STATED OTHERWISE THE POSITION OF ANY [ESG] SIZE HOLES ARE SUBJECT TO THE FOLLOWING GEOMETRIC TOLERANCES

ALL DIMENSIONS RELATIVE TO DATUM ARE SUBJECT TO THE FOLLOWING GEOMETRIC TOLERANCES

☒ 0.020 ☐ 0.040

TOLERANCES

xx = ± 0.13
x = ± 0.25
Holes = ± 0.08
Angles = ± 0.5°

DIMENSIONS mm. **DRAWN BY** M.A.P. **DATE** 31/01/08

SCALE NTS **DESIGN APPR'** M.A.P. **DATE** 31/01/08

PROJECTION **A3** **DIS** 5089 **SHT** 4 **REV** 4

DRAWING No. MRP1572 **REV** B

REV	B	8768	31/01/08
DCO No.			
DATE			