
ISSUE NUMBER **Mounting Option** THIS IS A C.A.D. GENERATED DRAWING 04-.156 (3.96) Dia. Mounting Holes DO NOT MAKE MANUAL REVISIONS TO MASTER. ORIGINAL 1 **Contact Detail** 558-90 Degree Bend (Code 541 Contacts) .156 [3.96] Contact Spacing x .200 [5.08] Row Spacing 4.834 [122.78] 4.688 [119.08] Card Slot Accepts .054 [1.37] to .070 [1.78] Thick P.C. Board 0.370 [9.40] 0.330[8.38] Card Slot .160 [4.06] Point of Contact 0.350[8.89] **SECTION A-A** ACAD REFERENCE NO. 837 ENG MASTER 837/887 Series High Temp Card Edge Connector DRAWN: J.LEE DATE: OCT. 06/09 Part Number: 887-029-558-104 **See Accompanying Pages for:** CHECKED: DATE: **Contact Bend Details** SHEET 1 OF 2 **EDAC INC** SCALE: THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC., AND TORONTO, ONTARIO SHALL NOT BE REPRODUCED, OR COPIED DRAWING NUMBER **ISSUE** CANADA OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS 837 Assembly YOUR CONNECTION TO QUALITY & SERVICE WITHOUT WRITTEN PERMISSION.



ISSUE NUMBER

ORIGINAL

1



	837/887 Series High Temp Card Edge Connector Contact Bend Detail		ACAD REFERENCE	NO. 837 EN	837 ENG MASTER	
			DRAWN: J.LEE	DATE: OC	DATE: OCT. 06/09	
			CHECKED:	DATE:	DATE:	
	EDAC INC TORONTO, ONTARIO CANADA YOUR CONNECTION TO QUALITY & SERVICE	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE: NTS	SHEET	2 OF 2	
			DRAWING NUMBER		ISSUE	
			837 Assembly		1	