


TOLERANCE UNLESS OTHERWISE SPECIFIED .X ±0.25 .XX ±0.13


.XXX ±0.10

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.




ISSUE NUMBER ORIGINAL PANEL CUT-OUT ADDED APRIL 2024 2





RECOMMENDED PANEL CUT-OUT



PANEL THICKNESS

1.50 ^{+0.50} 0.00

NOTES:

MATERIAL:

HOUSING: PA6T, UL94V-0

SHELL: STEEL, NICKEL PLATED

CONTACT: PRECISION MACHINED COPPER ALLOY

15µ GOLD PLATED

OPERATING TEMPERATURE: -25°C TO 85°C

CURRENT RATING: 5A PER CONTACT

CONTACT RESISTANCE: $10m\Omega$ MAX. **INSULATOR RESISTANCE:** 5000MΩ min.

DIELECTRIC

WITHSTANDING VOLTAGE: 1000V AC rms

DIM' TOLERANCE = ±0.05



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.

630W SERIES D-SUB CONNECTOR



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

SW REFERENCE NO.:	630W ASSEMBLY
DRAWN: C.B	DATE: AUG. 01/2018
CHECKED:	DATE:
SCALE: 1:1	SHEET 1 OF 1
DRAWING NUMBER: 6	330-W09-340-012 ISSUE

DRAWING NUMBER: 630-W09-340-012 PART NUMBER: 630-W09-340-012