





SPECIFIED		
.X	±0.25	
XX	±0.13	
XX	±0.10	

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.




ISSUE NUMBER ORIGINAL PANEL CUT-OUT ADDED APRIL 2024 2






## RECOMMENDED PANEL CUT-OUT



DIM' TOLERANCE = ±0.05



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.



PANEL THICKNESS

## NOTES:

MATERIAL:

**HOUSING:** PA6T, UL94V-0

SHELL: STEEL, NICKEL PLATED

CONTACT: PRECISION MACHINED COPPER ALLOY,

15µ GOLD PLATED

**OPERATING TEMPERATURE:** -25°C TO 85°C

**CURRENT RATING: 5A PER CONTACT** 

**CONTACT RESISTANCE:**  $10m\Omega$  MAX. **INSULATOR RESISTANCE:**  $5000M\Omega$  min.

**DIELECTRIC** 

WITHSTANDING VOLTAGE: 1000V AC rms

## 629W SERIES D-SUB CONNECTOR



EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

SW REFERENCE NO.: 629W	ASSEMBLY
DRAWN: C.B	DATE: AUG. 01/2018
CHECKED:	DATE:
SCALE: 1:1	SHEET 1 OF 1
DD 114110 111 14DED 000 14400	240.040

**ISSUE** DRAWING NUMBER: 629-W09-340-012 2 PART NUMBER: 629-W09-340-012