

# Han-Easy Lock ® 10/16/24B, QB



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 00 000 5221                                                                |
| Specification      | Han-Easy Lock ® 10/16/24B, QB                                                 |
| HARTING eCatalogue | <a href="https://harting.com/09000005221">https://harting.com/09000005221</a> |

## Identification

|                          |                |
|--------------------------|----------------|
| Category                 | Accessories    |
| Series of hoods/housings | Han® B         |
| Type of accessory        | Locking levers |

## Version

|                |                      |
|----------------|----------------------|
| Size           | 10 B                 |
|                | 16 B                 |
|                | 24 B                 |
| Locking type   | Double locking lever |
| Han-Easy Lock® | Yes                  |

## Material properties

|                                                            |                                                           |
|------------------------------------------------------------|-----------------------------------------------------------|
| Material (accessories)                                     | Polycarbonate (PC)                                        |
|                                                            | Stainless steel                                           |
| Colour (accessories)                                       | RAL 7037 (dust grey)                                      |
| Material flammability class acc. to UL 94 (locking levers) | V-0                                                       |
| RoHS                                                       | compliant                                                 |
| ELV status                                                 | compliant                                                 |
| China RoHS                                                 | e                                                         |
| REACH Annex XVII substances                                | Not contained                                             |
| REACH ANNEX XIV substances                                 | Not contained                                             |
| REACH SVHC substances                                      | Yes                                                       |
| REACH SVHC substances                                      | Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| ECHA SCIP number                     | 60b1a572-bb3f-476f-9307-b7d1688bd90c |
| California Proposition 65 substances | Yes                                  |
| California Proposition 65 substances | Nickel                               |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08)                 |
| Requirement set with Hazard Levels   | R22 (HL 1-3)                         |
|                                      | R23 (HL 1-3)                         |

## Commercial data

|                                |                                  |
|--------------------------------|----------------------------------|
| Packaging size                 | 10                               |
| Net weight                     | 15 g                             |
| Country of origin              | Germany                          |
| European customs tariff number | 85366990                         |
| GTIN                           | 5713140002265                    |
| eCl@ss                         | 27440392 Connector (accessories) |
| ETIM                           | EC002939                         |
| UNSPSC 24.0                    | 39121400                         |