

DIN-Signal high current m, 40A solder



Image is for illustration purposes only. Please refer to product description.

Part number	09 03 000 6135
Specification	DIN-Signal high current m, 40A solder
HARTING eCatalogue	https://harting.com/09030006135

Identification

Category	Contacts
Series	DIN 41612
Type of contact	PCB solder contact
Description of the contact	Straight
Contacts for	DIN 41612 Type M invers

Version

Termination method	Solder termination
Gender	Male contact for male connectors
Connection type	Motherboard to daughtercard
	Mezzanine
	PCB to cable
Manufacturing process	Turned contacts

Technical characteristics

Rated current	≤40 A
Insertion force	≤10 N
Withdrawal force	≥1.6 N
Performance level	1 acc. to IEC 60603-2
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
---------------------	--------------



Pushing Performance
Since 1945

Material properties

Surface (contacts)	Noble metal over Ni Mating side Sn over Ni Termination side
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	ecef7555-f643-4ceb-a337-fc54762297f1
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	DIN 41626
----------------	-----------

Commercial data

Packaging size	100
Net weight	1.814 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140003941
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques acc. to IEC 60512-5-2

