

DIN-Signal coax f, solder/crimp, 500hm



Part number	09 03 000 6274
Specification	DIN-Signal coax f, solder/crimp, 500hm
HARTING eCatalogue	https://harting.com/09030006274

Image is for illustration purposes only. Please refer to product description.

Identification

Series DIN 41612 har-modular® Type of contact Coaxial contact Straight With knurled area DIN 41612 Type M DIN 41612 Type M invers DIN 41612 Type MH 21+5	Category	Contacts
Type of contact Coaxial contact Description of the contact Straight With knurled area DIN 41612 Type M DIN 41612 Type M invers DIN 41612 Type MH 21+5	- 1	DIN 41612
Description of the contact Straight With knurled area DIN 41612 Type M DIN 41612 Type M invers DIN 41612 Type MH 21+5	Series	har-modular [®]
Description of the contact With knurled area DIN 41612 Type M DIN 41612 Type M invers DIN 41612 Type MH 21+5	Type of contact	Coaxial contact
DIN 41612 Type M DIN 41612 Type M invers DIN 41612 Type MH 21+5	Description of the contact	
DIN 41612 Type MH 21+5		DIN 41612 Type M
On the star form	Contacts for	
		DIN 41612 Type MH 21+5 DIN 41612 Bauform M 0+2
		har-modular [®] M module, male, angled
har-modular [®] M module, male, angled		har-modular [®] M module, male, straight

Version

Termination method	Solder termination
Termination method	Solder/crimp termination
Gender	Female contact for male connectors
	Motherboard to daughtercard
Connection type	Mezzanine
	Extender card
	PCB to cable
Manufacturing process	Turned contacts

Technical characteristics

Rated current	≤1.4 A
Insulation resistance	>10 ⁹ Ω



Technical characteristics

Contact resistance	≤10 mΩ for inner contact die ≤3 mΩ for outer ferrule
Impedance coaxial	50 Ω
Limiting temperature	-55 +125 °C
Return loss	>18 dB @ 1 GHz for cables RG 188 >15 dB @ 2 GHz for cables RG 188
Insertion force	≤10 N
Withdrawal force	≥1 N
Performance level	1
Mating cycles	≥500
Test voltage U _{r.m.s.}	0.75 kV
Frequency	2 GHz

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side
Material (locking)	Copper alloy
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	DIN 41626	
----------------	-----------	--

Commercial data

Packaging size	100	
----------------	-----	--



Commercial data

Net weight	2.01 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140004191
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors

Assembly instructions

