

Han TC300 male contact axial 95-120mm²




Image is for illustration purposes only. Please refer to product description.

Part number	09 11 000 6539
Specification	Han TC300 male contact axial 95-120mm ²
HARTING eCatalogue	https://harting.com/09110006539

Identification

Category	Contacts
Series	TC 300
Type of contact	Axial screw contact

Version

Termination method	Axial screw termination
Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	95 ... 120 mm ²
Rated current	≤300 A
Contact resistance	≤0.3 mΩ
Stripping length	19 ... 20 mm
Tightening torque	14 Nm @ 95 mm ² 16 Nm @ 120 mm ²
Wrench size	5 20
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	1
Net weight	73.78 g
Country of origin	Romania
European customs tariff number	85359000
GTIN	5713140188501
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522