

Han-Power S with 1x Han Q8/0; 2.5-4 mm²



Image is for illustration purposes only. Please refer to product description.

Part number	09 12 008 4801
Specification	Han-Power S with 1x Han Q8/0; 2.5-4 mm ²
HARTING eCatalogue	https://harting.com/09120084801

Identification

Category	Energy distributors
Series of hoods/housings	Han-Power® S
Element	Energy distributor
Specification	With 1x Han® Q 8/0 Female insert in Han-Compact® Hoods

Version

Termination method	IDC insulation displacement termination for stranded wires according to IEC 60228 Class 5
Number of contacts	8
PE contact	Yes

Technical characteristics

Conductor cross-section	2.5 ... 4 mm ²
Rated current	25 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Rated voltage acc. to CSA	600 V
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C



Pushing Performance
Since 1945

Technical characteristics

Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (contacts)	Copper alloy
Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material (locking)	Polyamide (PA) Fibre-glass reinforced
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	564b7d75-7bf6-4cfb-acb1-2168eb61b675
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	CE

Commercial data

Packaging size	1
Net weight	333 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140017856



Pushing Performance
Since 1945

Commercial data

eCl@ss	27142409 Small distribution board
ETIM	EC000214
UNSPSC 24.0	39121303