

## Han-Modular coax M-contact 75Ohm (RG179)



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 14 000 6121                                                                |
| Specification      | Han-Modular coax M-contact 75Ohm (RG179)                                      |
| HARTING eCatalogue | <a href="https://harting.com/09140006121">https://harting.com/09140006121</a> |

### Identification

|                            |                              |
|----------------------------|------------------------------|
| Category                   | Contacts                     |
| Series                     | DIN 41626                    |
| Type of contact            | Coaxial contact              |
| Description of the contact | for cables RG 179 BU, 187 AU |

### Version

|                       |                          |
|-----------------------|--------------------------|
| Termination method    | Solder termination       |
| Termination method    | Solder/crimp termination |
| Gender                | Male                     |
| Manufacturing process | Turned contacts          |

### Technical characteristics

|                    |                      |
|--------------------|----------------------|
| Rated current      | $\leq 1.5$ A         |
| Contact resistance | $\leq 10$ m $\Omega$ |
| Impedance coaxial  | 75 $\Omega$          |

### Material properties

|                     |                                                        |
|---------------------|--------------------------------------------------------|
| Material (contacts) | Copper alloy                                           |
| Surface (contacts)  | Gold plated                                            |
| RoHS                | compliant with exemption                               |
| RoHS exemptions     | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status          | compliant with exemption                               |
| China RoHS          | 50                                                     |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| REACH Annex XVII substances          | Not contained                        |
| REACH ANNEX XIV substances           | Not contained                        |
| REACH SVHC substances                | Yes                                  |
| REACH SVHC substances                | Lead                                 |
| ECHA SCIP number                     | b51e5b97-eeb5-438b-8538-f1771d43c17d |
| California Proposition 65 substances | Yes                                  |
| California Proposition 65 substances | Lead                                 |
|                                      | Nickel                               |

## Specifications and approvals

|                |             |
|----------------|-------------|
| Specifications | IEC 60664-1 |
|                | IEC 61984   |

## Commercial data

|                                |                                            |
|--------------------------------|--------------------------------------------|
| Packaging size                 | 10                                         |
| Net weight                     | 2 g                                        |
| Country of origin              | Hungary                                    |
| European customs tariff number | 85366990                                   |
| GTIN                           | 5713140018259                              |
| eCl@ss                         | 27440204 Contact for industrial connectors |
| ETIM                           | EC000796                                   |
| UNSPSC 24.0                    | 39121522                                   |