

## M23 P Hybrid 4+4+3+PE Female-C



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 612 3101
Specification	M23 P Hybrid 4+4+3+PE Female-C
HARTING eCatalogue	<a href="https://harting.com/09156123101">https://harting.com/09156123101</a>

### Identification

Category	Inserts
Series	Circular connectors M23
Identification	Hybrid
Element	Inserts

### Version

Termination method	Crimp termination
Gender	Female
Number of contacts	12
Number of data contacts	4
Number of signal contacts	4
Number of power contacts	3
Number of special contacts	1
Specification of special contacts	PE contact
Details	Please order crimp contacts separately.
	4x 2 mm
	4x 1 mm
	4x 0.6 mm

### Technical characteristics

Conductor cross-section	0.08 ... 4 mm <sup>2</sup>
Rated current (data)	2 A
Rated voltage (data)	60 V
Rated impulse voltage (data)	0.5 kV



**Pushing Performance**  
Since 1945

## Technical characteristics

Pollution degree (data)	3
Rated current (signal)	8 A
Rated voltage (signal)	300 V
Rated impulse voltage (signal)	2.5 kV
Pollution degree (signal)	3
Rated current (power)	28 A
Rated voltage (power)	600 V
Rated impulse voltage (power)	4 kV
Pollution degree (power)	3
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Test voltage $U_{r.m.s.}$	4 kV

## Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Blue
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

## Commercial data

Packaging size	5
Net weight	9 g
Country of origin	Germany
European customs tariff number	85366990



**Pushing Performance**  
Since 1945

Commercial data

GTIN	5713140187450
eCl@ss	27440223 Contact insert for circular connectors
ETIM	EC003557
UNSPSC 24.0	39121421