



Pushing Performance
Since 1945

SEK-18 SV MA STD STRWW RLG 64P PLS4




Image is for illustration purposes only. Please refer to product description.

Part number	09 18 564 5907
Specification	SEK-18 SV MA STD STRWW RLG 64P PLS4
HARTING eCatalogue	https://b2b.harting.com/09185645907

Identification

Category	Connectors
Series	SEK Standard
Element	Male connector
Description of the contact	Straight

Version

Termination method	Wrap termination
Connection type	PCB to cable
Number of contacts	64
Termination length	15 mm
Locking type	With long levers

Technical characteristics

Dimensions wire wrap post	0.6 x 0.6 mm
Contact rows	2
Contact spacing (termination side)	2.54 mm
Rated current	1 A
Insulation resistance	>10 ⁹ Ω
Contact resistance	≤20 mΩ
Limiting temperature	-55 ... +125 °C
Performance level	NM 30 (S4)
Mating cycles	≥250
Test voltage U _{r.m.s.}	1 kV



Pushing Performance
Since 1945

Technical characteristics

Isolation group	IIIa ($175 \leq CTI < 400$)
-----------------	-------------------------------

Material properties

Material (insert)	Thermoplastic resin (PBT)
Colour (insert)	Grey
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side Sn over Ni Termination side
Layer thickness	$\geq 0.76 \mu\text{m}$
Layer thickness	$\geq 30 \mu\text{inch}$
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 60603-13
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
Railway classification	F3/I3

Commercial data

Packaging size	50
Net weight	15.9 g
Country of origin	Switzerland
European customs tariff number	85366990



Pushing Performance
Since 1945

Commercial data

GTIN	5713140035591
ETIM	EC002637
eCl@ss	27460201 PCB connector (board connector)

Cross section of solder termination

