

## D SUB HD FE 15P SOLDER CUP PL3



Image is for illustration purposes only. Please refer to product description.

Part number	09 56 100 4704
Specification	D SUB HD FE 15P SOLDER CUP PL3
HARTING eCatalogue	<a href="https://harting.com/09561004704">https://harting.com/09561004704</a>

### Identification

Category	Connectors
Series	D-Sub
Identification	High Density
Element	Connector
Description of the contact	Stamped Straight

### Version

Termination method	Solder cup termination
Gender	Female
Size	D-Sub 1
Number of contacts	15
Locking type	Fixing flange with feed through hole Ø 3.1 mm

### Technical characteristics

Conductor cross-section	0.25 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 24
Rated current	2 A
Clearance distance	≥1 mm
Creepage distance	≥1 mm
Insulation resistance	> 5 x 10 <sup>9</sup> Ω
Contact resistance	<20 mΩ
Limiting temperature	-40 ... +85 °C (Soldering iron temperature during soldering: max. 350 °C for 3-5 s)



**Pushing Performance**  
Since 1945

## Technical characteristics

Performance level	3
Mating cycles	≥50
Test voltage $U_{r.m.s.}$	1 kV
Isolation group	IIIa ( $175 \leq CTI < 400$ )
Hot plugging	No

## Material properties

Material (insert)	Thermoplastic resin, glass-fibre filled (PBTP) Shell: steel, nickel plated
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side Sn over Ni Termination side
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	DIN 41652
----------------	-----------

## Commercial data

Packaging size	100
Net weight	6.714 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140071155
eCl@ss	27440214 D-Sub coupler
ETIM	EC001136



**Pushing Performance**  
Since 1945

## Commercial data

UNSPSC 24.0

39121469

---