

Han Yellock multiplier 2:3



Image is for illustration purposes only. Please refer to product description.

Part number	11 05 105 2802
Specification	Han Yellock multiplier 2:3
HARTING eCatalogue	https://b2b.harting.com/11051052802

Identification

Category	Inserts
Series	Han-Yellock®
Element	Multiplier
Specification	2 Bridged contacts 3 Unbridged contacts

Version

Gender	Female
Number of contacts	5

Technical characteristics

Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	≥ 500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 3000 (flame red)
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076
Approvals	DNV GL

Commercial data

Packaging size	2
Net weight	5.24 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140109681
ETIM	EC000438
eCl@ss	27440205 Contact insert for industrial connectors