

## Han B Hood Side Entry HC M32 stainl. peg



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 19 30 024 0507                                                                |
| Specification      | Han B Hood Side Entry HC M32 stainl. peg                                      |
| HARTING eCatalogue | <a href="https://harting.com/19300240507">https://harting.com/19300240507</a> |

### Identification

|                             |                    |
|-----------------------------|--------------------|
| Category                    | Hoods / Housings   |
| Series of hoods/housings    | Han <sup>®</sup> B |
| Type of hood/housing        | Hood               |
| Description of hood/housing | With stainless peg |
| Type                        | High construction  |

### Version

|                         |                                                   |
|-------------------------|---------------------------------------------------|
| Size                    | 24 B                                              |
| Version                 | Side entry                                        |
| Number of cable entries | 1                                                 |
| Cable entry             | 1x M32                                            |
| Locking type            | Double locking lever                              |
| Field of application    | Standard hoods/housings for industrial connectors |

### Technical characteristics

|                                        |                                                |
|----------------------------------------|------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Mating cycles                          | ≥500                                           |
| Degree of protection acc. to IEC 60529 | IP65                                           |
|                                        | IP66                                           |
|                                        | IP67                                           |



**Pushing Performance**  
 Since 1945

## Technical characteristics

|                                    |    |
|------------------------------------|----|
| Type rating acc. to UL 50 / UL 50E | 4  |
|                                    | 4X |
|                                    | 12 |

## Material properties

|                                      |                      |
|--------------------------------------|----------------------|
| Material (hood/housing)              | Aluminium die-cast   |
| Surface (hood/housing)               | Powder-coated        |
| Colour (hood/housing)                | RAL 7037 (dust grey) |
| RoHS                                 | compliant            |
| ELV status                           | compliant            |
| China RoHS                           | e                    |
| REACH Annex XVII substances          | Not contained        |
| REACH ANNEX XIV substances           | Not contained        |
| REACH SVHC substances                | Not contained        |
| California Proposition 65 substances | Yes                  |
| California Proposition 65 substances | Nickel               |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels   | R1 (HL 1-3)          |
|                                      | R7 (HL 1-3)          |

## Specifications and approvals

|           |        |
|-----------|--------|
| Approvals | CE     |
|           | DNV GL |

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 1                                        |
| Net weight                     | 240 g                                    |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140126855                            |
| eCl@ss                         | 27440202 Shell for industrial connectors |
| ETIM                           | EC000437                                 |
| UNSPSC 24.0                    | 39121466                                 |