


RECOMMENDED P.C. MOUNTING





| SWITCH FUNCTION |        |        |
|-----------------|--------|--------|
| POS. 1          | POS. 2 | POS. 3 |
|                 |        |        |
| ON              | OFF    | (ON)   |
| 2-3             | OPEN   | 2-1    |

(ON) = MOMENTARY



## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. PLATING MATERIAL: GOLD
5. RATING: 0.4 VOLT-AMPS MAX. @20V MAX. AC OR DC
6. ELECTRIC LIFE: 30,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
8. DIELECTRIC STRENGTH: 1,000 V RMS @SEA LEVEL.
9. OPERATING TEMP.: -30°C to 85°C
10. ▲ DENOTES CRITICAL PARAMETER.
11. 2011/65/EU (ROHS) COMPLIANT

▲ ACTUATOR COLOR:  
BLACKTERMINALS .76 X 1.27  
[.030 in X .050 in] TYP.

|     |        |                              |         |     |
|-----|--------|------------------------------|---------|-----|
| C   | 22709  | UPDATED LAYOUT AND TERMINALS | 2/20/17 | MJR |
| B   | 17532  | REVISED AND REDRAWN          | 8/3/07  | BF  |
| REV | PCR NO | DESCRIPTION                  | DATE    | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE 300AWSP5J6BLKVS21RE

SCALE  
2:1DATE  
7/25/2007DR  
BFDWG  
T301202REV  
C