



RECOMMENDED PANEL MOUNTING  
PANEL THICKNESS: 1.19 - 3.18mm




FRAME  
COLOR: BLACK

ACTUATOR  
COLOR: BLACK





| SWITCH FUNCTION |        |        |
|-----------------|--------|--------|
| POS. 1          | POS. 2 | POS. 3 |
|                 |        |        |
| ON              | NONE   | (ON)   |
| 2-3             | N/A    | 2-1    |

(ON)=MOMENTARY



## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. PLATING MATERIAL: SILVER
5. RATING: 2A @250VAC  
5A @120VAC or 28VDC
6. CONTACT RESISTANCE: 10 m $\Omega$  max. initial @ 2-4 VDC
7. ELECTRICAL LIFE: 40,000 make-and-break cycles  
at full load.
8. INSULATION RESISTANCE: 1,000 M $\Omega$  min.
9. DIELECTRIC STRENGTH: 1,000 V RMS @ sea level
10. OPERATING TEMP.: -40°C to 85°C
11. ▲ DENOTES CRITICAL PARAMETER.



| REV | ECO NO     | DESCRIPTION  | DATE     | BY | E-SWITCH®                |           |    |         | OBJECT ID |
|-----|------------|--------------|----------|----|--------------------------|-----------|----|---------|-----------|
| B   | ECO-101630 | print update | 02/06/23 | MW | TITLE 300SP2R6BLKM1QEBLK |           |    |         | 000025098 |
|     |            |              |          |    | SCALE                    | DATE      | DR | DWG     | REV       |
|     |            |              |          |    | 2:1                      | 6/18/2002 | CB | T312015 | B         |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO  
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED