

## LC connector singlemode 2mm



Image is for illustration purposes only. Please refer to product description.

Part number	20 10 125 8221
Specification	LC connector singlemode 2mm
HARTING eCatalogue	<a href="https://harting.com/20101258221">https://harting.com/20101258221</a>

### Identification

Category	Contacts
Series	LC
Type of contact	FO contact
Description of the contact	for singlemode
Features	for cable diameter up to 2 mm

### Version

Manufacturing process	Turned contacts
-----------------------	-----------------

### Technical characteristics

Limiting temperature	-40 ... +75 °C
----------------------	----------------

### Material properties

RoHS	compliant with exemption
RoHS exemptions	6(b) / 6(b)-II: Lead as an alloying element in aluminium containing up to 0,4 % lead by weight / Lead as an alloying element in aluminium for machining purposes with a lead content up to 0,4 % by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d



Pushing Performance  
Since 1945

Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Commercial data

Packaging size	2
Net weight	3 g
Country of origin	Germany
European customs tariff number	85367000
GTIN	5713140133655
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522