





CONTACT CONFIGURATION
TIMING: NON-SHORTING



NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NUMBERS FOR REFERENCE ONLY.
- ▲ 4. CONTACT MATERIAL: SILVER
5. CONTACT RATING: 150mA, 250VAC/DC
350mA, 110VAC/DC
6. CONTACT RATING (NON-SWITCHING) 5A
7. OPERATING FORCE: $.8 \pm .3$ kg-cm
8. OPERATING TEMP: -30°C to 85°C
- ▲ 9. CIRCUIT 2P: 6 POSITION 30° INDEX
10. DIELECTRIC STRENGTH: 500VAC FOR 1 MIN.
- ▲ 11. HARDWARE SUPPLIED ON SWITCH:
LOCKRING, LOCKWASHER and HEXNUT
12. ▲ DENOTES CRITICAL PARAMETER.



RECOMMENDED PCB LAYOUT

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
C	ECO-101206	redrawn and updated print	08/29/22	MW	KC26A30.001NPS				000012458
					SCALE	DATE	DR	DWG	REV
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					3:2	3/2/2001	CJB	G510450	C