





NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
 X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. TERMINAL/CONTACT MATERIAL: SILVER PLATED
5. RATING: 3A @ 250VAC
6. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
7. ELECTRICAL LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD
8. ACTUATION FORCE: 1 POLE (SP) 2.5 ± 1.0 N
9. MECHANICAL LIFE: 500,000 (LOCKING) CYCLES
10. INSULATION RESISTANCE: 1,000MΩ @ 500VDC MIN.
11. DIELECTRIC STRENGTH: 2,000 RMS @ SEA LEVEL
12. OPERATING TEMPERATURE: -20°C to 55°C
13. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 14. LAMP VOLTAGE: N/A
15. TRAVEL: 3.2mm
16. MOUNTING NUT TORQUE: 0.3 - 0.5Nm
17. INGRESS PROTECTION: IP65
18. HARDWARE SUPPLIED: GASKET and MOUNTING NUT



REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH®				OBJECT ID
A	ECO-100889	Release	08/19/22	MR					100121928
					TITLE LB22F23Q7				
					SCALE 1:1	DATE 4/29/2022	DR MW	DWG T942005	REV A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
 E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED