

HARAX M8-XS male 3-pole



Image is for illustration purposes only. Please refer to product description.

Part number	21 02 159 1305
Specification	HARAX M8-XS male 3-pole
HARTING eCatalogue	https://harting.com/21021591305

Identification

Category	Connectors
Series	Circular connectors M8
Identification	M8-XS
Element	Cable connector
Specification	Straight

Version

Termination method	HARAX [®] connection technology
Gender	Male
Shielding	Unshielded
Number of contacts	3
Coding	A-coding
Locking type	Screw locking

Technical characteristics

Conductor cross-section	0.1 ... 0.14 mm ²
Conductor cross-section [AWG]	AWG 27 ... AWG 26
Wire outer diameter	≤1 mm
Rated current	2 A
Rated voltage	32 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Overvoltage category	III



Pushing Performance
Since 1945

Technical characteristics

Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Tightening torque	0.4 Nm
Wrench size (knurled screw / knurled nut)	9
Limiting temperature	-40 ... +85 °C
Mating cycles	≥ 100
Degree of protection acc. to IEC 60529	IP67 locked condition
Cable diameter	1.9 ... 3.5 mm
Isolation group	I ($600 \leq \text{CTI}$)

Material properties

Material (insert)	Polyamide (PA)
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material (hood/housing)	Polyamide (PA) Zinc die-cast
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 61076-2-104
----------------	-----------------



Pushing Performance
Since 1945

Commercial data

Packaging size	1
Net weight	11.5 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140136960
ETIM	EC002635
eCl@ss	27440116 Circular connector (for field assembly)