




O.P. (MM)	P.T. (MM)
20.7 ± 1.5	5.5 MAX.



O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



CIRCUIT: SPST N.O.

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X $\pm$ 0.4
X.XX $\pm$ 0.25
3. RATING: .4VA AT 20VAC/VDC MAX
- ▲ 4. OPERATING FORCE: 120 $\pm$ 40 GRAMS
5. OPERATING TEMP: -25°C TO 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
9. DIELECTRIC STRENGTH: 1500VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 MILLI -OHMS MAX.
11. ▲ DENOTES CRITICAL PARAMETER.



REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH®					OBJECT ID
B	ECO-100843	REMOVE VDE RATING AND LOGO	05/03/22	JS						000021086
					TITLE LS085R106F120C1C					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 3:2	DATE 7/18/2012	DR RC	DWG Q950102	REV B	