

# Gerätebuchse M12-A-kod. IP67 5pol.



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 21 03 321 6520                                                                |
| Specification      | Gerätebuchse M12-A-kod. IP67 5pol.                                            |
| HARTING eCatalogue | <a href="https://harting.com/21033216520">https://harting.com/21033216520</a> |

## Identification

|               |                               |
|---------------|-------------------------------|
| Category      | Connectors                    |
| Series        | Circular connectors M12       |
| Element       | PCB adapter                   |
| Specification | Straight<br>for rear mounting |

## Version

|                    |                                    |
|--------------------|------------------------------------|
| Termination method | Reflow soldering termination (THR) |
| Gender             | Female                             |
| Shielding          | Shielded                           |
| Number of contacts | 5                                  |
| Coding             | A-coding                           |
| Locking type       | Screw locking                      |

## Technical characteristics

|                       |                           |
|-----------------------|---------------------------|
| Rated current         | 4 A                       |
| Rated voltage         | 60 V                      |
| Rated impulse voltage | 1.5 kV                    |
| Pollution degree      | 3                         |
| Overvoltage category  | III                       |
| Insulation resistance | $>10^8 \Omega$            |
| Contact resistance    | $\leq 10 \text{ m}\Omega$ |
| Tightening torque     | 2 Nm Lock nut             |



**Pushing Performance**  
Since 1945

## Technical characteristics

|                                        |                      |
|----------------------------------------|----------------------|
| Limiting temperature                   | -40 ... +85 °C       |
| Mating cycles                          | ≥100                 |
| Degree of protection acc. to IEC 60529 | IP67 mated condition |
| Isolation group                        | I (600 ≤ CTI)        |

## Material properties

|                                           |                                                        |
|-------------------------------------------|--------------------------------------------------------|
| Material (insert)                         | Polyamide (PA)                                         |
| Material (contacts)                       | Copper alloy                                           |
| Surface (contacts)                        | Au over Ni Mating side                                 |
| Material (hood/housing)                   | Zinc die-cast                                          |
| Material flammability class acc. to UL 94 | V-0                                                    |
| RoHS                                      | compliant with exemption                               |
| RoHS exemptions                           | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                                | compliant with exemption                               |
| China RoHS                                | 50                                                     |
| REACH Annex XVII substances               | Not contained                                          |
| REACH ANNEX XIV substances                | Not contained                                          |
| REACH SVHC substances                     | Yes                                                    |
| REACH SVHC substances                     | Lead                                                   |
| ECHA SCIP number                          | 0d7d3693-d625-47ab-934a-d241bf72c86e                   |
| California Proposition 65 substances      | Yes                                                    |
| California Proposition 65 substances      | Lead<br>Nickel                                         |
| Fire protection on railway vehicles       | EN 45545-2 (2020-08)                                   |
| Requirement set with Hazard Levels        | R26                                                    |

## Specifications and approvals

|                |                 |
|----------------|-----------------|
| Specifications | IEC 61076-2-101 |
|----------------|-----------------|

## Commercial data

|                                |          |
|--------------------------------|----------|
| Packaging size                 | 10       |
| Net weight                     | 20 g     |
| Country of origin              | Romania  |
| European customs tariff number | 85366990 |



**Pushing Performance**  
Since 1945

## Commercial data

|        |                                          |
|--------|------------------------------------------|
| GTIN   | 5713140137868                            |
| ETIM   | EC002637                                 |
| eCl@ss | 27460201 PCB connector (board connector) |