







NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X $\pm$ 0.4
X.XX $\pm$ 0.25
3. TERM. NOS. FOR REFERENCE ONLY.

5. MATERIALS:

CONTACT/TERMINALS: SILVER PLATE

HOUSING: PBT UL94VO

BASE: PA66 UL94VO

ACTUATOR: PA66 UL94V0

6. CONTACT RESISTANCE: 100 MILLI-OHM (INITIAL)

▲ 7. TIMING: NON-SHORTING

8. OPERATING FORCE: 230± 50GF

9. TRAVEL: MOMENTARY

2MM TO MAKE

3MM OVERALL

10. ELECTRICAL LIFE: 10000 CYCLES

11. OPERATING TEMP: -20°C TO +70°C

12. $\blacktriangle$ DENOTES CRITICAL PARAMETER:

13. 2002/95/EC (ROHS) COMPLIANT



B	19670	UPDATE CIRCUIT DIAGRAM	2/10/11	BGL
A	16400	RELEASED FOR PRODUCTION	8/31/06	BO
REV	PCR NO	DESCRIPTION	DATE	BY
TITLE PBH2UOANAGV				

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED	SCALE 2.5:1	DATE 8/31/2006	DR BO	DWG Q960019	REV B
---	----------------	-------------------	----------	----------------	----------