





▲ SWITCH FUNCTION

POS. 1	POS. 2
OFF	(ON)
OPEN	1-2

(ON) = MOMENTARY



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NOS. FOR REF. ONLY
- RATING: 2A @ 36VDC
- CONTACT RESISTANCE: 50mΩ MAX.
- INSULATION RESISTANCE: 100MΩ @ 500VDC
- DIELECTRIC STRENGTH: 1,500V, RMS 50Hz, 1 MINUTE
- ELECTRICAL LIFE: 200,000 CYCLES
9. CONTACT MATERIAL: SILVER
- OPERATING TEMPERATURE: -40°C to 85°C
- INGRESS PROTECTION: IP67
- LED VOLTAGE: 1.8V 20mA (Forward), 2.8V 20mA (Reverse)
- ▲ DENOTES CRITICAL PARAMETER
- HARDWARE INCLUDED: HEX NUT and O-RING (NOT SHOWN)

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
D	ECO-102661	print release	05/02/24	MW	PV0H240SS-3G1				000002307
					SCALE	DATE	DR	DWG	REV
					2:1	10/6/2017	MW	52-PV0H240SS3G1	D

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED