



▲ SWITCH FUNCTION

POS. 1	POS. 2
OFF	(ON)
OPEN	1-2

(ON) = MOMENTARY



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NOS. FOR REF. ONLY
- RATING: 2A @ 36VDC
- CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
- INSULATION RESISTANCE: 1,000MΩ @ 500VDC
- DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
- ELECTRICAL LIFE: 200,000 CYCLES
- CONTACT MATERIAL: SILVER
- OPERATING TEMPERATURE: -20°C to 55°C
- INGRESS PROTECTION: IP65
- ▲ 12. LED VOLTAGE: 1.8V 20mA (Forward), 2.8V 20mA (Reverse)
- ▲ 13. ▲ DENOTES CRITICAL PARAMETER
14. HARDWARE INCLUDED: HEX NUT AND O-RING (NOT SHOWN)



E-SWITCH®

OBJECT ID
000002308

B	24583	HOUSING UPDATE	11/9/20	JM
A	23201	NEW RELEASE	2/2/18	MJR
REV	PCR NO	DESCRIPTION	DATE	BY

TITLE PV0H240SS-3K1

SCALE
2:1DATE
2/2/2018DR
MJRDWG
52-PV0H240SS3K1REV
B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED