

## SHEET 1 OF 1



11.0 [.43in]

## SWITCH FUNCTION POS. 1 POS. 2 ON (ON) 1-3 (1-2)

( ) = MOMENTARY





## NOTE:

- 1. ALL DIMENSIONS IN MM [INCH]
- 2. GENERAL TOLERANCE:  $X.X = \pm 0.4$

 $X.XX = \pm 0.25$ 

- 3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: GOLD
- 5. RATING: 2A 24VDC
- 6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
- 7. INSULATION RESISTANCE: 1,000 MΩ MIN.
- 8. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
- 9. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
- 10. OPERATING TEMP.: -20°C to 55°C
- ▲ 11. TRAVEL: 2.8mm
  - 12. A DENOTES CRITICAL PARAMETER.
- ▲ 13. LAMP VOLTAGE: 2.8V
  - 14. INGRESS PROTECTION: IP65
- 15. HARDWARE SUPPLIED: O-RING AND HEXNUT





THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PV4F2B0SSG-341-M26

SCALE 3:2 DATE 5/29/2018

DR MW

DWG 52-PV4S00269

REV

Α