


- 6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
- 7. INSULATION RESISTANCE: 1,000 MΩ MIN.
- 8. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
- 9. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
- 10. OPERATING TEMP.: -20°C to 55°C
- ▲11. TRAVEL: 2.8mm
- 12. ▲ DENOTES CRITICAL PARAMETER.
- ▲13. LAMP VOLTAGE: 12V
- 14. INGRESS PROTECTION: IP65
- 15. HARDWARE SUPPLIED: O-RING AND HEXNUT



Α	22017	RELEASE FOR PRODUCTION	10/8/15	MW
REV	PCR NO	DESCRIPTION	DATE	BY
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY				

TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E+SWITCH\*

PV4F2B0SS-314

**SCALE** DATE 3:2 10/8/2015 DR MW DWG 52-PV4F2B0SS314 **REV** 

Α