



Pushing Performance
Since 1945

M23_19P FE,Int-thread,STR PUR cable,5M



Image is for illustration purposes only. Please refer to product description.

Part number	21 37 350 0D74 050
Specification	M23_19P FE,Int-thread,STR PUR cable,5M
HARTING eCatalogue	https://harting.com/21373500D74050

Identification

Category	System cabling
Series	Circular connectors M23
Identification	Signal
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M23 Female Straight
Type of cable	Copper cable (round)
Features	Flame retardancy Oil and UV resistant Highly EMC resistant Halogen freeness

Version

Cable length	5 m
Number of cores	19
Core structure	3x AWG 18 + 16x AWG 22

Technical characteristics

Rated voltage	150 V
Rated current (signal)	2 A
Rated current (power)	9 A
Limiting temperature	-40 ... +80 °C



Pushing Performance
 Since 1945

Technical characteristics

Degree of protection acc. to IEC 60529	IP67
--	------

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (cable)	PUR (polyurethane)
Colour (cable)	Black
Material (overmoulding)	Thermoplastic polyurethane (TPU)
Colour (overmoulding)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	1
Net weight	965 g
Country of origin	China
European customs tariff number	85444290
GTIN	5713140241183
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line