



RECOMMENDED PANEL MOUNTING

PANEL THICKNESS	X
0.70-1.25	19.1-19.2
1.25-2.00	19.3-19.4
2.00-3.00	19.4-19.6






NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. RATING: 6A @250VAC (cURus)
9A @125VAC (cURus)
4(1)A @250VAC (VDE)
- ▲ 4. LAMP VOLTAGE: 24VDC (LED)
5. MATERIAL:
CONTACT SURFACE: COIN SILVER, SILVER PLATE
TERMINAL: COPPER ALLOY W/SILVER PLATE.
6. CONTACT RESISTANCE: $< 20\text{m}\Omega$
7. INSULATION RESISTANCE: $> 1000\text{M}\Omega$
8. DIELECTRIC STRENGTH: $> 1500\text{V RMS min. @SEA LEVEL}$
9. MECHANICAL LIFE: 30,000 CYCLES.
10. ELECTRICAL LIFE: 10,000 CYCLES
11. ▲ DENOTES CRITICAL PARAMETER.

▲ I/O SYMBOL
COLOR: WHITE

▲ HOUSING: BLACK



C	24416	Incandescent Bulb to LED	7/23/20	MW
B	22376	Changed Description	7/5/16	MW
A	11692	RELEASED	10/1/01	CJB
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE R1973ABLKRILFF4

SCALE
3:2DATE
10/1/2001DR
CJBDWG
M400063REV
C