

Han PushPull Power L Aida Kupplung



Image is for illustration purposes only. Please refer to product description.

Part number	61 04 201 1085 01
Specification	Han PushPull Power L Aida Kupplung
HARTING eCatalogue	https://harting.com/6104201108501

Identification

Category	Connectors
Series	Han® PushPull (V14)
Identification	Power L
Element	Connector sets
Specification	AIDA compliant Coupling
Features	Intuitive locking mechanism Field assembly without tools

Version

Termination method	Spring clamp termination
Number of contacts	5
Locking type	PushPull
Pack contents	Hoods / Housings Panel feed through Cable gland Head cap screw M3x8 enclosed in loose form

Technical characteristics

Conductor cross-section	0.75 ... 2.5 mm²
Conductor cross-section [AWG]	AWG 18 ... AWG 13
Rated current	16 A
Rated voltage	24 V
Rated impulse voltage	4 kV
Pollution degree	3



Pushing Performance
Since 1945

Technical characteristics

Stripping length	10 mm Conductors 44 mm cable jacket
Tightening torque	3 Nm
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (insert)	Polyamide (PA)
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side Sn over Ni Termination side
Material (hood/housing)	Metal
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	IEC/PAS 61076-3-126
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	164.955 g
Country of origin	Germany



Pushing Performance
Since 1945

Commercial data

European customs tariff number	85366990
GTIN	5713140223882
eCl@ss	27440114 Rectangular connector (for field assembly)
ETIM	EC002636
UNSPSC 24.0	39121408