





| O.P. (MM) | P.T. (MM) |
|-----------|-----------|
| 8.8 ±0.8  | 1.6 Max.  |





O.P. = OPERATING POINT  
P.T. = PRE-TRAVEL



CIRCUIT: SPDT  
NORMALLY CLOSED

## NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X±0.4  
X.XX±0.25
- RATING: 3A @125VAC  
1.5A @250 VAC UL
- OPERATING FORCE: 40±10 GRAMS
- OPERATING TEMP: -25°C TO 75°C
- ELECTRICAL LIFE: 10,000 CYCLES MIN.
- INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
- DIELECTRIC STRENGTH: 500VAC - 1 MINUTE
- ▲ DENOTES CRITICAL PARAMETER.
- PACKAGED IN TRAYS, 120 PIECES PER TRAY



| REV                                                                                                          | ECO NO     | DESCRIPTION  | DATE     | BY | E-SWITCH®              |           |     |         | OBJECT ID |
|--------------------------------------------------------------------------------------------------------------|------------|--------------|----------|----|------------------------|-----------|-----|---------|-----------|
| B                                                                                                            | ECO-102049 | PRINT UPDATE | 07/03/23 | JS | TITLE SS0750301F040V2A |           |     |         | 000021351 |
| THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED |            |              |          |    | SCALE                  | DATE      | DR  | DWG     | REV       |
|                                                                                                              |            |              |          |    | 4:1                    | 5/30/2012 | DRG | Q971035 | B         |